



Dimensions [in. (mm)]			
Model	A	B	C
DM-6L	0.24 +0.008 (6 +0.2)	3.33 (85)	2.50 (63.6)
DM-13L	0.51 +0.008 (13 +0.2)	3.73 (95)	3.06 (77.6)
DM-25L	0.98 +0.008 (25 +0.2)	4.88 (124)	4.09 (101.6)