



Dimensions [in. (mm)]

Model	A	B	C	D	E	F	G
50105-01	1.94 (49.3)	N/A	1.52 (38.6)	0.94 (24.0)	12.0°	23.6°	6.30 (160.0)
50105-02	1.94 (49.3)	0.383 (9.72)	1.52 (38.6)	0.94 (24.0)	12.0°	23.6°	N/A
50102-01	1.94 (49.3)	N/A	1.52 (38.6)	0.41 (10.4)	15.0°	30°	6.30 (160.0)
50102-02	1.94 (49.3)	0.212 (5.3)	1.52 (38.6)	0.41 (10.4)	15.0°	30°	N/A