



Model	Diameter [in. (mm)]		Dimensions [in. (mm)]		
	A	B	C	D	E
UPA2	2.06 (52.4)	2.00 (50.8)	0.76 (19.4)	0.51 (13.1)	0.45 (11.5)
UPA1	1.06 (27.0)	1.00 (25.4)	0.50 (12.7)	0.25 (6.4)	0.202 (5.1)
UPA.75	0.812 (20.6)	0.75 (19.1)	0.48 (12.2)	0.23 (5.8)	0.163 (4.1)
UPA.5	0.562 (14.3)	0.50 (12.7)	0.42 (10.7)	0.17 (4.3)	0.107 (2.7)