



Model	Dimensions [in. (mm)]					
	A	B	C	D	DIM E EXT THREAD	DIM F INT THREAD
LT05-05	0.70 (17.8)	0.54 (13.7)	0.45 (11.4)	0.47 (11.9)	0.535-40	0.535-40
LT05-10	0.70 (17.8)	1.04 (26.4)	0.45 (11.4)	0.97 (24.6)	0.535-40	0.535-40
LT10-05	1.20 (30.5)	0.54 (13.7)	0.90 (22.9)	0.47 (11.9)	1.035-40	1.035-40
LT10-10	1.20 (30.5)	1.04 (26.4)	0.90 (22.9)	0.97 (24.6)	1.035-40	1.035-40
LT10-20	1.20 (30.5)	2.04 (51.8)	0.90 (22.9)	1.97 (50.0)	1.035-40	1.035-40
LT10-30	2.20 (55.9)	3.04 (77.2)	0.90 (22.9)	2.97 (75.4)	1.035-40	1.035-40
LT20-05	2.20 (55.9)	0.54 (13.7)	1.90 (48.3)	0.47 (11.9)	2.035-40	2.035-40
LT20-10	2.20 (55.9)	1.04 (26.4)	1.90 (48.3)	0.97 (24.6)	2.035-40	2.035-40
LT20-20	2.20 (55.9)	2.04 (51.8)	1.90 (48.3)	1.97 (50.0)	2.035-40	2.035-40
LT20-30	2.20 (55.9)	3.04 (77.2)	1.90 (48.3)	2.97 (75.4)	2.035-40	2.035-40