



Model (Metric)	Length [in.(mm)]		Diameter [in.(mm)]		Thread	
	A		B	C	D	E
SP-0.75 (M-SP-0.75)	0.75 (19.1)		–	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-1 (M-SP-1)	1.0 (25.4)		–	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-1.5 (M-SP-1.5)	1.5 (38.1)		–	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-2 (M-SP-2)	2.0 (50.8)		0.1 (2.5)	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-2.5 (M-SP-2.5)	2.5 (63.5)		0.1 (2.5)	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-3 (M-SP-3)	3.0 (76.2)		0.1 (2.5)	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-3.5 (M-SP-3.5)	3.5 (88.9)		0.1 (2.5)	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-4 (M-SP-4)	4.0 (101.6)		0.1 (2.5)	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-6 (M-SP-6)	6.0 (152.4)		0.1 (2.5)	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-8 (M-SP-8)	8.0 (203.2)		0.1 (2.5)	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)
SP-12 (M-SP-12)	12.0 (304.8)		0.1 (2.5)	0.5 (12.7)	8-32 (M4)	1/4-20 (M6)