



Model	A	B	C	øD
CT26.35BM	2.11 (53.6)	0.85 (21.5)	1.89 ± 0.08 (48 ± 2)	1.38 (35)
CT26.44BM	2.28 (58)	1.02 (26)	2.07 ± 0.08 (52.5 ± 2)	1.73 (44)
CT26.50BM	2.40 (61)	1.14 (29)	2.19 ± 0.08 (55.5 ± 2)	1.97 (50)