



	A	B	C
TRA6	3.94 (100)	.59 (15)	.81 ⁺²⁴ ₀ (20.5 ⁺⁶ ₀)
TRA12	4.45 (113)	.59 (15)	.66 ⁺⁴⁹ ₀ (16.8 ^{+12.5} ₀)
TRA25	4.72 (120)	.71 (18)	.66 ⁺⁹⁸ ₀ (16.8 ⁺²⁵ ₀)