



Dimensions [in. (mm)]

Model	H	h
SL-600-N10	10.0 (254)	N/A
SL-600-N13.5	13.5 (343)	1.7 (43.2)
SL-600-N16	16.0 (406)	3.8 (96.5)
SL-600-N19.5	19.5 (495)	7.3 (185.4)
SL-600-N22	22.0 (559)	9.8 (248.9)
SL-600-N23.5	23.5 (597)	11.3 (287.0)
SL-600-N28	28.0 (711)	15.8 (401.3)
SL-1200-N10	10.0 (254)	N/A
SL-1200-N13.5	13.5 (343)	1.7 (43.2)
SL-1200-N16	16.0 (406)	3.8 (96.5)
SL-1200-N19.5	19.5 (495)	7.3 (185.4)
SL-1200-N22	22.0 (559)	9.8 (248.9)
SL-1200-N23.5	23.5 (597)	11.3 (287.0)
SL-1200-N28	28.0 (711)	15.8 (401.3)