



Model	Dimensions						
	A	B	C	D	E Max.	F Min.	F Max.
VLH-1A	2.00 (50.8)	2.74 (69.6)	0.63 (16.0)	2.50 (63.5)	3.07 (80.0)	0.25 (6.3)	1.25 (31.8)
VLH-3A	4.00 (101.6)	4.74 (120.3)	1.00 (25.4)	5.00 (127)	5.56 (141.2)	0.60 (15.2)	3.60 (91.4)