



MODEL NO.	DIM A	DIM B
GW3036-PG4-L	30 in (762 mm)	36 in (914 mm)
GW3036-PG4-H	30 in (762 mm)	36 in (914 mm)
GW3648-PG4-H	36 in (914 mm)	48 in (1219 mm)
GW3660-PG4-H	36 in (914 mm)	60 in (1524 mm)
M-GW3036-PG4-L	29.5 in (750 mm)	35.4 in (900 mm)
M-GW3036-PG4-H	29.5 in (750 mm)	35.4 in (900 mm)
M-GW3648-PG4-H	35.4 in (900 mm)	47.2 in (1200 mm)
M-GW3660-PG4-H	35.4 in (900 mm)	59.1 in (1500 mm)