



Model	Dimensions [in. (mm)]			Thread	D	E	Dimensions [in. (mm)]			H	K	L
	A	B Min	B Max				C	e	F			
B18-15.5	0.71 (18)	0.05 (1.2)	0.31 (8)	0.800-36 (M20.25 RMS)	0.94 (24)	0.17 (4.25)	0.02 (0.5)	0.67 (17)	0.61 (15.5)	0.24 (6)	0.22 (5.5)	
B18-26	0.71 (18)	0.05 (1.2)	0.31 (8)	0.800-36 (M20.25 RMS)	0.94 (24)	0.17 (4.25)	0.02 (0.5)	0.67 (17)	1.02 (26)	0.24 (6)	0.22 (5.5)	
B18-38	0.71 (18)	0.05 (1.2)	0.31 (8)	0.800-36 (M20.25 RMS)	0.94 (24)	0.17 (4.25)	0.02 (0.5)	0.67 (17)	1.50 (38)	0.24 (6)	0.22 (5.5)	
B18-56	0.71 (18)	0.05 (1.2)	0.31 (8)	0.800-36 (M20.25 RMS)	0.94 (24)	0.17 (4.25)	0.02 (0.5)	0.67 (17)	2.20 (56)	0.24 (6)	0.22 (5.5)	
B19	0.75 (19.05)	0.05 (1.2)	0.31 (8)	M25 x 0.75	1.14 (29)	0.17 (4.25)	0.02 (0.5)	0.71 (18)	0.61 (15.5)	0.24 (6)	0.22 (5.5)	
B22.4	0.88 (22.4)	0.05 (1.2)	0.31 (8)	M25 x 0.75	1.14 (29)	0.17 (4.25)	0.02 (0.5)	0.83 (21)	0.61 (15.5)	0.24 (6)	0.22 (5.5)	
B25.4	1.00 (25.4)	0.06 (1.6)	0.39 (10)	M30 x 0.75	1.34 (34)	0.20 (5)	0.03 (0.75)	0.94 (24)	0.61 (15.5)	0.24 (6)	0.26 (6.5)	
B31.5	1.24 (31.5)	0.06 (1.6)	0.43 (11)	M35 x 0.75	1.54 (39)	0.20 (5)	0.03 (0.75)	1.18 (30)	0.69 (17.5)	0.24 (6)	0.26 (6.5)	
B38.1	1.50 (38.1)	0.06 (1.6)	0.55 (14)	M45 x 0.75	1.93 (49)	0.22 (5.5)	0.03 (0.75)	1.42 (36)	0.81 (20.5)	0.26 (6.5)	0.30 (7.5)	
B40	1.57 (40)	0.06 (1.6)	0.55 (14)	M45 x 0.75	1.93 (49)	0.22 (5.5)	0.03 (0.75)	1.50 (38)	0.81 (20.5)	0.26 (6.5)	0.30 (7.5)	
B50	1.97 (50)	0.06 (1.6)	0.79 (20)	M55 x 0.75	2.32 (59)	0.23 (5.75)	0.03 (0.75)	1.89 (48)	1.06 (27)	0.26 (6.5)	0.30 (7.5)	
B50.8	2.00 (50.8)	0.06 (1.6)	0.79 (20)	M55 x 0.75	2.32 (59)	0.23 (5.75)	0.03 (0.75)	1.93 (49)	1.06 (27)	0.26 (6.5)	0.30 (7.5)	
B63	2.48 (63)	0.09 (2.2)	0.83 (21)	M68 x 0.75	2.91 (74)	0.24 (6)	0.04 (1)	2.40 (61)	1.08 (27.5)	0.33 (8.5)	0.35 (9)	
B76.2	3.00 (76.2)	0.05 (1.2)	0.91 (23)	M85 x 0.75	3.70 (94)	0.28 (7)	0.04 (1)	2.91 (74)	1.14 (29)	0.33 (8.5)	0.35 (9)	
B80	3.15 (80)	0.05 (1.2)	0.91 (23)	M85 x 0.75	3.70 (94)	0.28 (7)	0.04 (1)	3.07 (78)	1.14 (29)	0.33 (8.5)	0.35 (9)	
B95	3.74 (95)	0.06 (1.6)	1.06 (27)	M105 x 0.75	4.69 (119)	0.25 (6.25)	0.03 (0.75)	3.66 (93)	1.36 (34.5)	0.33 (8.5)	0.35 (9)	
B100	3.94 (100)	0.06 (1.6)	1.06 (27)	M105 x 0.75	4.69 (119)	0.25 (6.25)	0.03 (0.75)	3.86 (98)	1.36 (34.5)	0.33 (8.5)	0.35 (9)	
B101.6	4.00 (101.6)	0.06 (1.6)	1.06 (27)	M105 x 0.75	4.69 (119)	0.25 (6.25)	0.03 (0.75)	3.90 (99)	1.36 (34.5)	0.33 (8.5)	0.35 (9)	