




4 HOLES, THD A, $\varnothing 1.89$ (48) 3 HOLES, THD B CLR, D SPACING



4 HOLES, THD A, $\varnothing 3.62$ (92)



17 HOLES, THD B, D SPACING

2 ACCESS HOLES, $\varnothing .45$ (11.5) D SPACING

4 HOLES, THD A CLR, $\varnothing 1.89$ (48)

Model (M- Metric)	Thread			Dimensions [in. (mm)]		
	A	B	C	D	E	F
UMR12.40	10-24	1/4-20	M18x1	1.000 in.	5.61 in.	
M-UMR12.40	M5	M6	M18x1	25.0 mm	142.5 mm	
UMR12.63	10-24	1/4-20	M18x1	1.000 in.	6.56 in.	
M-UMR12.63	M5	M6	M18x1	25.0 mm	166.5 mm	
UMR12.80	10-24	1/4-20	M22x1	1.000 in.	8.29 in.	1.38 in.
M-UMR12.80	M5	M6	M22x1	25.0 mm	210.5 mm	35 mm