



Dimensions [in. (mm)]

Thread

Model	A	B		C	D	E	F		G
		Min	Max				Min	Max	
BM11.5	1.36 (34.5)	1.00 (25.5)	1.20 (30.5)	0.43 (11)	0.16 (4)	0.13 (3.2)	0.03 (0.8)	0.23 (5.8)	M6 x 0.50
BM11.10	2.01 (51)	1.40 (35.5)	1.79 (45.5)	0.43 (11)	0.16 (4)	0.19 (4.7)	0.03 (0.8)	0.43 (10.8)	M6 x 0.50
BM11.16	2.24 (57)	1.40 (35.5)	2.03 (51.5)	0.43 (11)	0.16 (4)	0.19 (4.7)	0.03 (0.8)	0.66 (16.8)	M6 x 0.50
BM11.25	3.00 (76.2)	1.81 (46)	2.80 (71)	0.43 (11)	0.16 (4)	0.19 (4.7)	0.02 (0.5)	0.98 (25)	M6 x 0.50
BM17.25	3.25 (82.5)	1.95 (49.5)	2.93 (74.5)	0.67 (17)	0.28 (7.2)	0.28 (7.2)	0.03 (0.8)	1.01 (25.8)	M12 x 0.50
BM17.51	5.43 (138)	3.04 (77.1)	5.04 (128.1)	0.67 (17)	0.28 (7.2)	0.28 (7.2)	0.09 (2.4)	2.10 (53.4)	M12 x 0.50
BM25.40	4.92 (125)	2.72 (69)	4.29 (109)	0.98 (25)	0.31 (8)	0.57 (14.5)	0.12 (3)	1.69 (43)	M18 x 1.00
BM25.63	6.79 (172.5)	3.70 (94)	6.18 (157)	0.98 (25)	0.31 (8)	0.57 (14.5)	0.04 (1)	2.52 (64)	M18 x 1.00
BM32.80	8.35 (212)	4.17 (106)	7.32 (186)	1.26 (32)	0.47 (12)	0.94 (24)	0.08 (2)	3.23 (82)	M22 x 1.00