



Model	A	B
PS-0.031-T	0.031 in.	1/4-20 (M6) CLR
PS-0.063-T	0.063 in.	1/4-20 (M6) CLR
PS-0.125-T	0.125 in.	1/4-20 (M6) CLR
PS-0.25-T	0.250 in.	1/4-20 (M6) CLR
PS-0.031	0.031 in.	8-32 (M4) CLR
PS-0.063	0.063 in.	8-32 (M4) CLR
PS-0.125	0.125 in.	8-32 (M4) CLR
PS-0.25	0.250 in.	8-32 (M4) CLR