



Retaining Ring

Model	Thread		Dimensions [in. (mm)]							
	A	B	C	D	E	F	G	H	J	
LPLH-25T	0.875-20	0.281-32	0.98 (24.9)	0.38 (9.7)	0.125 (3.2)	0.03 (0.8)	0.187 (4.7)	0.187 (4.7)	0.093 (2.4)	
LPLH-50T	0.875-20	0.546-32	0.98 (24.9)	0.38 (9.7)	0.125 (3.2)	0.03 (0.8)	0.437 (11.1)	0.398 (10.1)	0.093 (2.4)	
LPLH-75T	0.875-20	0.775-32	0.98 (24.9)	0.38 (9.7)	0.125 (3.2)	0.03 (0.8)	0.687 (17.4)	0.625 (15.9)	0.093 (2.4)	
LPLH-1T	1.438-20	1.063-20	1.63 (41.4)	0.50 (12.7)	0.125 (3.2)	0.06 (1.6)	0.93 (23.6)	0.755 (19.2)	0.125 (3.2)	
LPLH-1.5T	2.063-20	1.563-20	2.25 (57.2)	0.60 (15.2)	0.100 (2.5)	0.100 (2.5)	1.375 (34.9)	1.18 (30.0)	0.125 (3.2)	