



Model (Metric)	Thread		Dimensions [in. (mm)]		
	A	B	C	D	E
TGN80	8-32 (M4)	1/4-20 (M6)	1.000 (25.0)		3.000 (75.0)
TGN120	10-24 (M5)	1/4-20 (M6)	1.000 (25.0)	2.000 (50.0)	
TGN160	1/4-20 (M6)	1/4-20 (M6)	1.000 (25.0)		4.000 (100.0)