



Dimensions [in. (mm)]			
Model	DIM A THREAD	DIM B THICKNESS	DIM C CLEAR APERTURE
LT05-RR	0.535-40	0.08 (2.0)	0.43 (10.9)
LT10-RR	1.035-40	0.08 (2.0)	0.90 (22.9)
LT15-RR	1.535-40	0.10 (2.5)	1.40 (35.6)
LT20-RR	2.035-40	0.10 (2.5)	1.87 (47.5)
LT30-RR	3.035-40	0.10 (2.5)	2.80 (71.1)
LT30M-RR	M30.5 X 0.5	0.08 (2.0)	1.10 (28.0)