



Dimensions [in. (mm)]

Model	H	h
RL-2000-N10	10.0 (254)	N/A
RL-2000-N13.5	13.5 (343)	1.7 (43.2)
RL-2000-N16	16.0 (406)	3.8 (96.5)
RL-2000-N19.5	19.5 (495)	7.3 (185.4)
RL-2000-N22	22.0 (559)	9.8 (248.9)
RL-2000-N23.5	23.5 (597)	11.3 (287.0)
RL-2000-N28	28.0 (711)	15.8 (401.3)