



Model	Dimensions [in. (mm)]		Thread
	A	B	
AJS170-0.5K-NL	1.27 (32.3)	0.50 (12.7)	1/4-170
AJS170-0.5H-NL	1.29 (32.8)	0.50 (12.7)	1/4-170
AJS127-02H	1.23 (31.2)	0.25 (6.4)	1/4-127
AJS127-0.5H	1.43 (36.3)	0.50 (12.7)	1/4-127
AJS127-0.5	1.41 (35.8)	0.50 (12.7)	1/4-127
AJS100-02H	1.23 (31.2)	0.25 (6.4)	1/4-100
AJS100-0.5H-NL	1.29 (32.8)	0.50 (12.7)	1/4-100
AJS100-0.5H	1.43 (36.3)	0.50 (12.7)	1/4-100
AJS100-0.5K-NL	1.27 (32.3)	0.50 (12.7)	1/4-100
AJS100-0.5K	1.41 (35.8)	0.50 (12.7)	1/4-100
AJS100-0.5	1.41 (35.8)	0.50 (12.7)	1/4-100
AJS100-1H	2.10 (53.3)	1.00 (25.4)	1/4-100
AJS100-1	2.10 (53.3)	1.00 (25.4)	1/4-100
AJS100-2	2.97 (75.4)	2.00 (50.8)	1/4-100
AJS8-100-02H	0.88 (22.4)	0.25 (6.4)	8-100
AJS8-100-0.5H	1.16 (29.5)	0.50 (12.7)	8-100
AJS8-100-0.5	1.16 (29.5)	0.50 (12.7)	8-100
AJS8-100-1	1.85 (47.0)	1.00 (25.4)	8-100
AJS20-0.5	1.41 (35.8)	0.50 (12.7)	1/4-20
AJS20-1	2.10 (53.3)	1.00 (25.4)	1/4-20
AJS20-2	2.97 (75.4)	2.00 (50.8)	1/4-20