



Model (Metric)	Thread F
SB19.18	0.800-36 (M20.25 RMS)
SB19.22.4	M25 x 0.75
SB19.25.4	M30 x 0.75
M-SB19.31.5	M35 x 0.75
SB32.18	0.800-36 (M20.25 RMS)
SB32.22.4	M25 x 0.75
SB32.25.4	M30 x 0.75
M-SB32.31.5	M35 x 0.75
SB32.40	M45 x 0.75
SB32.50	M55 x 0.75
M-SB63	M68 x 0.75
SB80	M85 x 0.75
M-SB100	M105 x 0.75

Model (Metric)	Thread		Dimensions [in. (mm)]		
	A	B	C	D	E
SB19- (M-SB19-)	4-40 (M3)	1/4-20 (M6)	0.33 (8.5)	0.77 (19.5)	1.93 (49)
SB32- (M-SB32-)	4-40 (M3)	1/4-20 (M6)	0.49 (12.5)	1.28 (32.5)	3.11 (79)
M-SB63	M3	M6	0.55 (14)		3.11 (79)
SB80 (M-SB80)	4-40 (M3)	1/4-20 (M6)	0.55 (14)		4.25 (108)
M-SB100	M3	M6	0.55 (14)		5.04 (128)