



Model	Dimensions [in. (mm)]				
	A	B	C	D	E
UPA1-.5	0.196 (5.0)	0.236 (6.0)	ø1.00 (ø25.4)	ø0.438 (ø11.1)	ø0.50 (ø12.7)
UPA1-.75	0.196 (5.0)	0.236 (6.0)	ø1.00 (ø25.4)	ø0.710 (ø18.0)	ø0.75 (ø19.1)
UPA2-1	0.236 (6.0)	0.50 (12.7)	ø2.00 (ø50.8)	ø0.918 (ø23.3)	ø1.00 (ø25.4)
UPA-OM	THRU	0.236 (6.0)	ø1.00 (ø25.4)	ø0.800* (ø20.3)*	

* UPA-OM: Inside diameter has 0.800-36 (M20.25) RMS threads.