



| Model      | Dimensions [in. (mm)] |             |
|------------|-----------------------|-------------|
|            | A                     | B           |
| Q-TMS-0.75 | .75 (19.1)            | 0.28 (7.1)  |
| Q-TMS-1    | 1.0 (25.4)            | 0.28 (7.1)  |
| Q-TMS-1.5  | 1.5 (38.1)            | 0.50 (12.7) |
| Q-TMS-2    | 2.0 (50.8)            | 0.50 (12.7) |
| Q-TMS-3    | 3.0 (76.2)            | 0.50 (12.7) |
| Q-TMS-4    | 4.0 (101.6)           | 0.50 (12.7) |