



Model	L_1	L_2
F-C5-F2-1310	8.12 mm	22.32 mm, EFL = 11.26 mm
F-C5-F2-1550	8.16 mm	22.36 mm, EFL = 11.32 mm
F-C5-F2-543	7.79 mm	21.99 mm, EFL = 10.90 mm
F-C5-F2-780	7.97 mm	22.17 mm, EFL = 11.10 mm