



MODEL	A in. [mm]	B in. [mm]	*C in.	*D [mm]
TF-36-28-I	67.6 [1717]	31.6 [803]	28.3	[720]
TF-38-28-I	91.6 [2327]	31.6 [803]	28.3	[720]
TF-46-28-I	67.6 [1717]	43.6 [1107]	28.3	[720]
TF-48-28-I	91.6 [2327]	43.6 [1107]	28.3	[720]
TF-410-28-I	115.6 [2936]	43.6 [1107]	28.3	[720]
TF-56-28-I	67.6 [1717]	55.6 [1412]	28.3	[720]
TF-58-28-I	91.6 [2327]	55.6 [1412]	28.3	[720]
TF-510-28-I	115.6 [2936]	55.6 [1412]	28.3	[720]
TF-36-24-I	67.6 [1717]	31.6 [803]	24.3	[618]
TF-38-24-I	91.6 [2327]	31.6 [803]	24.3	[618]
TF-46-24-I	67.6 [1717]	43.6 [1107]	24.3	[618]
TF-48-24-I	91.6 [2327]	43.6 [1107]	24.3	[618]
TF-410-24-I	115.6 [2936]	43.6 [1107]	24.3	[618]
TF-56-24-I	67.6 [1717]	55.6 [1412]	24.3	[618]
TF-58-24-I	91.6 [2327]	55.6 [1412]	24.3	[618]



NOTE: *Measured to top of frame. Height may vary slightly due to floating; leveling feet are adjustable.