



<b>Model</b>	<b>Diameter</b>	<b>Thickness</b>
FSW10	5.0 mm	1.0 mm
FSW11	10.0 mm	1.3 mm
FSW12	12.5 mm	1.5 mm
FSW13	15.0 mm	2.0 mm
FSW14	20.0 mm	2.0 mm
FSW15	25.0 mm	3.0 mm
FSW16	30.0 mm	4.0 mm
FSW17	40.0 mm	4.0 mm
FSW18	50.0 mm	5.0 mm
FSW19	12.5 mm	2.0 mm