


Model	A - Dimensions (mm x mm)	t - Thickness (mm)
10SJ00ER.3	25.4 x 25.4	3.175
20SJ00ER.3	50.8 x 50.8	3.175
75J00ER.3	190.5 x 190.5	3.175
75K00ER.3	190.5 x 190.5	5.842