



| PART NUMBER | A REF<br>in [mm] | B<br>in [mm] | C<br>in [mm] |
|-------------|------------------|--------------|--------------|
| OHS-4       | 48 [ 1200]       | 53.8 [1367]  | 58 [1473]    |
| OHS-5       | 60 [ 1500]       | 65.8 [1671]  | 70 [1778]    |
| OHS-6       | 72 [ 1800]       | 77.8 [1976]  | 82 [2083]    |
| OHS-8       | 96 [ 2400]       | 101.8 [2586] | 106 [2692]   |
| OHS-10      | 120 [ 3000]      | 125.8 [3195] | 130 [3302]   |
| OHS-12      | 144 [ 3600]      | 149.8 [3805] | 154 [3912]   |

NOTES:

1. DIMS IN [ ] ARE IN mm.