



| VIS SYSTEM         | DIM A   | DIM B   | DIM C<br>in. | DIM D<br>in. |
|--------------------|---------|---------|--------------|--------------|
| VIS3030-XXX-325N   | 30.0 in | 30.0 in | 32.8         | 32.8         |
| VIS3036-XXX-325N   | 30.0 in | 36.0 in | 32.8         | 38.8         |
| VIS3048-XXX-325N   | 30.0 in | 48.0 in | 32.8         | 50.8         |
| VIS3636-XXX-325N   | 36.0 in | 36.0 in | 38.8         | 38.8         |
| VIS3648-XXX-325N   | 36.0 in | 48.0 in | 38.8         | 50.8         |
| VIS3660-XXX-325N   | 36.0 in | 60.0 in | 38.8         | 62.8         |
| VIS3672-XXX-325N   | 36.0 in | 72.0 in | 38.8         | 74.8         |
| M-VIS3030-XXX-325N | 750 mm  | 750 mm  | 32.8         | 32.8         |
| M-VIS3036-XXX-325N | 750 mm  | 900 mm  | 32.8         | 38.8         |
| M-VIS3048-XXX-325N | 750 mm  | 1200 mm | 32.8         | 50.8         |
| M-VIS3636-XXX-325N | 900 mm  | 900 mm  | 38.8         | 38.8         |
| M-VIS3648-XXX-325N | 900 mm  | 1200 mm | 38.8         | 50.8         |
| M-VIS3660-XXX-325N | 900 mm  | 1500 mm | 38.8         | 62.8         |
| M-VIS3672-XXX-325N | 900 mm  | 1800 mm | 38.8         | 74.8         |

