

Part Number	Table Size	Distance Between Legs in. [mm]	No. of Casters
TB-46	4FT X 6FT	36.0 X 40.0 [914 X 1016]	0
TBC-46	4FT X 6FT	36.0 X 40.0 [914 X 1016]	4
TB-48	4FT X 8FT	36.0 X 52.0 [914 X 1321]	0
TBC-48	4FT X 8FT	36.0 X 52.0 [914 X 1321]	4
TB-410	4FT X 10FT	36.0 X 66.0 [914 X 1676]	0
TBC-410	4FT X 10FT	36.0 X 66.0 [914 X 1676]	4
TB-412	4FT X 12FT	36.0 X 80.0 [914 X 2032]	0
TBC-412	4FT X 12FT	36.0 X 80.0 [914 X 2032]	4
TB-56	5FT X 6FT	48.0 X 40.0 [1219 X 1016]	0
TBC-56	5FT X 6FT	48.0 X 40.0 [1219 X 1016]	4
TB-58	5FT X 8FT	48.0 X 52.0 [1219 X 1321]	0
TBC-58	5FT X 8FT	48.0 X 52.0 [1219 X 1321]	4
TB-510	5FT X 10FT	48.0 X 66.0 [1219 X 1676]	0
TBC-510	5FT X 10FT	48.0 X 66.0 [1219 X 1676]	4
TB-512	5FT X 12FT	48.0 X 80.0 [1219 X 2032]	0
TBC-512	5FT X 12FT	48.0 X 80.0 [1219 X 2032]	4
M-TB-46	1200mm X 1800mm	35.24 X 38.87 [895 X 987]	0
M-TBC-46	1200mm X 1800mm	35.24 X 38.87 [895 X 987]	4
M-TB-48	1200mm X 2400mm	35.24 X 50.49 [895 X 1282]	0
M-TBC-48	1200mm X 2400mm	35.24 X 50.49 [895 X 1282]	4
M-TB-410	1200mm X 3000mm	35.24 X 64.11 [895 X 1628]	0
M-TBC-410	1200mm X 3000mm	35.24 X 64.11 [895 X 1628]	4
M-TB-412	1200mm X 3600mm	35.24 X 77.73 [895 X 1974]	0
M-TBC-412	1200mm X 3600mm	35.24 X 77.73 [895 X 1974]	4
M-TB-56	1500mm X 1800mm	47.06 X 38.87 [1195 X 987]	0
M-TBC-56	1500mm X 1800mm	47.06 X 38.87 [1195 X 987]	4
M-TB-58	1500mm X 2400mm	47.06 X 50.49 [1195 X 1282]	0
M-TBC-58	1500mm X 2400mm	47.06 X 50.49 [1195 X 1282]	4
M-TB-510	1500mm X 3000mm	47.06 X 64.11 [1195 X 1628]	0
M-TBC-510	1500mm X 3000mm	47.06 X 64.11 [1195 X 1628]	4
M-TB-512	1500mm X 3600mm	47.06 X 77.73 [1195 X 1974]	0
M-TBC-512	1500mm X 3600mm	47.06 X 77.73 [1195 X 1974]	4

