



MODEL NUMBER	A in. [mm]	B in. [mm]	C in. [mm]	D in. [mm]	E in. [mm]	F in	G mm
M-OTS-xxx-36-8-I	35.4 [900]	70.9 [1800]	8 [203]	31.6 [803]	67.6 [1717]	36.7	932
M-OTS-xxx-38-8-I	35.4 [900]	94.5 [2400]	8 [203]	31.6 [803]	91.6 [2327]	36.7	932
M-OTS-xxx-46-8-I	47.2 [1200]	70.9 [1800]	8 [203]	43.6 [1107]	67.6 [1717]	36.7	932
M-OTS-xxx-48-8-I	47.2 [1200]	94.5 [2400]	8 [203]	43.6 [1107]	91.6 [2327]	36.7	932
M-OTS-xxx-410-8-I	47.2 [1200]	118.1 [3000]	8 [203]	43.6 [1107]	115.6 [2936]	36.7	932
M-OTS-xxx-56-8-I	59.06 [1500]	70.9 [1800]	8 [203]	55.6 [1412]	67.6 [1717]	36.7	932
M-OTS-xxx-510-8-I	59.06 [1500]	118.1 [3000]	8 [203]	55.6 [1412]	115.6 [2936]	36.7	932
M-OTS-xxx-46-12-I	47.2 [1200]	70.9 [1800]	12 [305]	43.6 [1107]	67.6 [1717]	40.7	1034
M-OTS-xxx-48-12-I	47.2 [1200]	94.5 [2400]	12 [305]	43.6 [1107]	91.6 [2327]	40.7	1034
M-OTS-xxx-410-12-I	47.2 [1200]	118.1 [3000]	12 [305]	43.6 [1107]	115.6 [2936]	40.7	1034
M-OTS-xxx-56-12-I	59.06 [1500]	70.9 [1800]	12 [305]	55.6 [1412]	67.6 [1717]	40.7	1034
M-OTS-xxx-510-12-I	59.06 [1500]	118.1 [3000]	12 [305]	55.6 [1412]	115.6 [2936]	40.7	1034

NOTES:

- xxx = ST, UT2, OR UT Series Table.
- DIMS IN [ ] ARE IN mm.