



Model	W	L	T	Mounting Holes	# of Microlocks
PG-12-2-ML	1 ft.	2 ft.	2.3 in.	1/4-20	4
PG-13-2-ML	1 ft.	3 ft.	2.3 in.	1/4-20	4
PG-14-2-ML	1 ft.	4 ft.	2.3 in.	1/4-20	5
PG-22-2-ML	2 ft.	2 ft.	2.3 in.	1/4-20	5
PG-23-2-ML	2 ft.	3 ft.	2.3 in.	1/4-20	5
PG-24-2-ML	2 ft.	4 ft.	2.3 in.	1/4-20	5
PG-25-2-ML	2 ft.	5 ft.	2.3 in.	1/4-20	5
PG-26-2-ML	2 ft.	6 ft.	2.3 in.	1/4-20	5
PG-30x30-2-ML	30 in.	30 in.	2.3 in.	1/4-20	5
PG-30x36-2-ML	30 in.	36 in.	2.3 in.	1/4-20	5
PG-30x48-2-ML	30 in.	48 in.	2.3 in.	1/4-20	5
PG-33-2-ML	3 ft.	3 ft.	2.3 in.	1/4-20	5
PG-34-2-ML	3 ft.	4 ft.	2.3 in.	1/4-20	5
PG-35-2-ML	3 ft.	5 ft.	2.3 in.	1/4-20	5
PG-36-2-ML	3 ft.	6 ft.	2.3 in.	1/4-20	5

M-PG-12-2-ML	300 mm	600 mm	59 mm	M6	4
M-PG-13-2-ML	300 mm	900 mm	59 mm	M6	4
M-PG-14-2-ML	300 mm	1200 mm	59 mm	M6	5
M-PG-22-2-ML	600 mm	600 mm	59 mm	M6	5
M-PG-23-2-ML	600 mm	900 mm	59 mm	M6	5
M-PG-24-2-ML	600 mm	1200 mm	59 mm	M6	5
M-PG-25-2-ML	600 mm	1500 mm	59 mm	M6	5
M-PG-26-2-ML	600 mm	1800 mm	59 mm	M6	5
M-PG-30x30-2-ML	750 mm	750 mm	59 mm	M6	5
M-PG-30x36-2-ML	750 mm	900 mm	59 mm	M6	5
M-PG-30x48-2-ML	750 mm	1200 mm	59 mm	M6	5
M-PG-33-2-ML	900 mm	900 mm	59 mm	M6	5
M-PG-34-2-ML	900 mm	1200 mm	59 mm	M6	5
M-PG-35-2-ML	900 mm	1500 mm	59 mm	M6	5
M-PG-36-2-ML	900 mm	1800 mm	59 mm	M6	5
PG-12-4-ML	1 ft.	2 ft.	4.3 in.	1/4-20	4
PG-13-4-ML	1 ft.	3 ft.	4.3 in.	1/4-20	4
PG-14-4-ML	1 ft.	4 ft.	4.3 in.	1/4-20	5
PG-22-4-ML	2 ft.	2 ft.	4.3 in.	1/4-20	5
PG-23-4-ML	2 ft.	3 ft.	4.3 in.	1/4-20	5
PG-24-4-ML	2 ft.	4 ft.	4.3 in.	1/4-20	5
PG-25-4-ML	2 ft.	5 ft.	4.3 in.	1/4-20	5
PG-26-4-ML	2 ft.	6 ft.	4.3 in.	1/4-20	5
PG-30x30-4-ML	30 in.	30 in.	4.3 in.	1/4-20	5
PG-30x36-4-ML	30 in.	36 in.	4.3 in.	1/4-20	5
PG-30x48-4-ML	30 in.	48 in.	4.3 in.	1/4-20	5
PG-33-4-ML	3 ft.	3 ft.	4.3 in.	1/4-20	5
PG-34-4-ML	3 ft.	4 ft.	4.3 in.	1/4-20	5
PG-35-4-ML	3 ft.	5 ft.	4.3 in.	1/4-20	5
PG-36-4-ML	3 ft.	6 ft.	4.3 in.	1/4-20	5
M-PG-12-4-ML	300 mm	600 mm	110 mm	M6	4
M-PG-13-4-ML	300 mm	900 mm	110 mm	M6	4
M-PG-14-4-ML	300 mm	1200 mm	110 mm	M6	5
M-PG-22-4-ML	600 mm	600 mm	110 mm	M6	5
M-PG-23-4-ML	600 mm	900 mm	110 mm	M6	5
M-PG-24-4-ML	600 mm	1200 mm	110 mm	M6	5
M-PG-25-4-ML	600 mm	1500 mm	110 mm	M6	5
M-PG-26-4-ML	600 mm	1800 mm	110 mm	M6	5
M-PG-30x30-4-ML	750 mm	750 mm	110 mm	M6	5
M-PG-30x36-4-ML	750 mm	900 mm	110 mm	M6	5
M-PG-30x48-4-ML	750 mm	1200 mm	110 mm	M6	5
M-PG-33-4-ML	900 mm	900 mm	110 mm	M6	5
M-PG-34-4-ML	900 mm	1200 mm	110 mm	M6	5
M-PG-35-4-ML	900 mm	1500 mm	110 mm	M6	5
M-PG-36-4-ML	900 mm	1800 mm	110 mm	M6	5