


Filter: P1L12

Color: Green
Material: Polycarbonate
VLT: 30%



Optical Density (OD):

- 180 - 315 D LB9 + IR LB4 + M LB6Y (OD 9+)
- >315 - 445 DIRM LB6 (OD 6+)
- 705 - <720 DIRM LB4 (OD 4+)
- 720 - <735 DIRM LB5 (OD 5+)
- 735 - <745 DIRM LB6 (OD 6+)
- 745 - <755 D LB6 + IRM LB7 (OD 7+)
- 755 - 1100 D LB6 + IR LB8 + M LB8Y (OD 8+)
- 0,01W 2x10E-6J 630-650 RB1
- LVU CE




F29.P1L12.5000



Labels

F29.P1L12.5000


180 - 315 D LB9 + IR LB4 + M LB6Y (OD 9+)
 >315 - 445 DIRM LB6 (OD 6+)
 705 - <720 DIRM LB4 (OD 4+)
 720 - <735 DIRM LB5 (OD 5+)
 735 - <745 DIRM LB6 (OD 6+)
 745 - <755 D LB6 + IRM LB7 (OD 7+)
 755 - 1100 D LB6 + IR LB8 + M LB8Y (OD 8+)
 0,01W 2x10E-6J 630-650 RB1
 LVU CE



CE **MM/YYYY**
VLT 30%

Manufactured by:
 LASERVISION USA, LP
 595 Phalen Boulevard
 Saint Paul, MN 55130
 info@lasersafety.com | lasersafety.com
 P.800-393-5565

Markings *Illustration, may vary slightly from final product.*



Contact: Tom Poole
 t.poole@lasersafety.com
 Phone: 651-357-1801

 Authorized Customer Signature

 Date

 Authorized Laservision Signature

 Date