



Model	Dimensions [in. (mm)]				
	A	B	C	DIM D EXT THREAD	DIM E INT THREAD
LT05-F	0.70 (17.8)	1.05 (26.7)	0.45 (11.4)	0.535-40	0.535-40
LT10-F	1.20 (30.5)	1.05 (26.7)	0.94 (23.9)	1.035-40	1.035-40
LT20-F	1.20 (30.5)	1.55 (39.4)	1.94 (49.3)	2.035-40	2.035-40