



	Thread	Dimensions [in. (mm)]				
Model (Metric)	A	B	C	D	E	F
34	1/4-20 (M6)	0.50 (12.5)	1.0 (25.0)	0.50 (13.1)	0.75 (19.7)	1.00 (25.6)
300-P	1/4-20 (M6)	0.50 (12.5)	1.0 (25.0)	2.00 (1.97)	2.13 (2.13)	