

Newport Part No.	REO Part No.	Description	Head PN	Power Supply PN	Legacy REO Description
<b>Tunable HeNe Laser Systems</b>					
R-30602	30602	LASER SYSTEM, TUNABLE, 115V			LSTP-1010 (115v)
R-30603	30603	LASER SYSTEM, TUNABLE, 230V			LSTP-1010 (230v)
<b>Stabilized HeNe Laser Systems, Red 633nm</b>					
R-39727	39727	LASER SYSTEM, 633NM, STBLZD, >1.2MW	R-39728H	R-32733PS	
R-32734	32734	LASER SYSTEM, 633NM, STBLZD, >1.5MW	R-32732H	R-32733PS	
R-14286	14286	OEM LASER SYSTEM. 633NM, .STABLZD,1.5MW			
<b>Red (633nm) HeNe Laser Systems</b>					
R-31008	31008	LASER SYSTEM, 633NM, 0.5MW, RAN	R-39698H	R-39783PS	
R-31007	31007	LASER SYSTEM, 633NM, 0.8MW, POL	R-39697H	R-39783PS	
R-31005	31005	LASER SYSTEM, 633NM, 1.5MW, RAN	R-30404H	R-39783PS	
R-30025	30025	LASER SYSTEM, 633NM, 1.5MW,POL, 9.5"	R-30028H	R-39783PS	
R-30988	30988	LASER SYSTEM, 633NM, 2.0MW, RAN	R-30629H	R-39783PS	LHRR-0200
R-30989	30989	LASER SYSTEM, 633NM, 2.0MW, POL	R-30621H	R-39783PS	LHRP-0201
R-30990	30990	LASER SYSTEM, 633NM, 5.0MW, RANDOM	R-30630H	R-39783PS	LHRR-0500
R-30991	30991	LASER SYSTEM, 633NM, 5.0MW, POL	R-30623H	R-39783PS	LHRP-0501
R-30992	30992	LASER SYSTEM, 633NM, 12.0MW, RANDOM	R-30633H	R-39785PS	LHRR-1200
R-30993	30993	LASER SYSTEM, 633NM, 12.0MW, POL	R-30624H	R-39785PS	LHRP-1201
R-39635	39635	LASER SYSTEM, 633NM, 17.0MW, RANDOM	R-30635H	R-39786PS	LHRR-1700
R-30995	30995	LASER SYSTEM, 633NM, 17.0MW, POL	R-30625H	R-39786PS	LHRP-1701
R-31425	31425	LASER SYSTEM, 633NM, 35MW,POL,115V	R-30627H	R-30582PS	LSRP-3501
R-32413	32413	LASER SYSTEM, 633NM, 35MW,POL,230V	R-30627H	R-30584PS	LSRP-3501
R-14309	14309	LASER SYSTEM, 633NM, 35MW, POL			
<b>Green (543nm) HeNe Laser Systems</b>					
R-40141	40141	LASER SYSTEM, 543NM, 0.5mW, Multimode	R-30683H	R-39783PS	
R-30967	30967	LASER SYSTEM, 543NM, 0.5MW, RAN	R-30605H	R-39783PS	LHGR-0050
R-30968	30968	LASER SYSTEM, 543NM, 0.5MW, POL	R-30682H	R-39783PS	LHGP-0051
R-39568	39568	LASER SYSTEM, 543NM, 1.0MW, RAN	R-30532H	R-39783PS	
R-39581	39581	LASER SYSTEM, 543NM, 1.0MW, POL	R-30526H	R-39784PS	
R-33361	33361	LASER SYSTEM, 543NM, 1.5MW, POL	R-32656H	R-39784PS	LHGP-0151
R-30972	30972	LASER SYSTEM, 543NM, 2.0MW, RAN	R-30609H	R-39784PS	LHGR-0200
<b>Yellow (594nm) HeNe Laser Systems</b>					
R-40094	40094	LASER SYSTEM, 594NM, 1.0MW, POL	R-30571H	R-39783PS	
R-39582	39582	LASER SYSTEM, 594NM, 2.0MW, POL	R-30639H	R-39783PS	LHYP-0201
<b>Orange (612nm) HeNe Laser Systems</b>					
R-40139	40139	LASER SYSTEM, 612nm, 2.0mW, Pol	R-30616H	R-39783PS	
R-40140	40140	LASER SYSTEM, 612nm, 2.5mW, Random	R-30618H	R-39783PS	
<b>Infrared HeNe Laser Systems</b>					
R-40136	40136	LASER SYSTEM, 1.15um, 1.0mW, Pol	R-30684H	R-39785PS	
R-33141	33141	LASER SYSTEM, 1.52UM, 1.0MW, POL	R-30612H	R-39785PS	LHIP-0101-152
R-32172	32172	LASER SYSTEM, 3.39UM, 2.0MW, POL	R-30685H	R-39785PS	LHIP-0201-339

Dual HeNe Laser Systems					
R-40137	40137	LASER SYSTEM, 1523/633nm, 1.0mW, POL	R-30538H	R-39785PS	
R-40138	40138	LASER SYSTEM, 1.15/3.39um, 5.0mW, POL	R-30615H	R-39785PS	
OPIS HeNe Laser Systems					
R-14354	14354	LASER SYSTEM, 633NM, 3MW, OPIS, ORTH POL		R-39783PS	

**Laser Heads Only**

Newport Part No.	REO Part No.	Description	Power Supply PN	Legacy REO Description	Old REO Head PN
R-30615H	30615	Laser Head for R-40138, 1.15/3.39um, 5.0mW POL	39785	LHIP-0501-115/339	30547
R-30538H	30538	Laser Head for R-40137, 1523/633nm, 1.0mW, POL	39785	LHIP-0101-152/633	30540
R-30684H	30684	Laser Head for R-40136, 1.15um, 1.0mW, Pol	39785	N/A	30541
R-30616H	30616	Laser Head for R-40139, 612nm, 2.0mW, Pol	39783	LHOP-0201	30549
R-30618H	30618	Laser Head for R-40140, 612nm, 2.5mW, Random	39783	N/A	30551
R-30683H	30683	Laser Head for R-40141, 543nm, 0.5mW, Multimode	39783	LHGR-0050M	30530
R-30404H	30404	LASER HEAD FOR R-31005, 633NM, 1.5MW, RAN	39783		39636
R-30621H	30621	LASER HEAD FOR R-30989, 633NM, 2.0MW, POL	39783	LHRP-0201	30554
R-30623H	30623	LASER HEAD FOR R-30991, 633NM, 5.0MW, POL	39783	LHRP-0501	30555
R-30625H	30625	LASER HEAD FOR R-30995, 633NM, 17.0MW, POL	39786	LHRP-1701	30557
R-30609H	30609	LASER HEAD FOR R-30972, 543NM, 2.0MW, RAN	39784	LGHR-0200	30536
R-32732H	32732	LASER HEAD FOR R-32734, 633NM, STBLZD, >1.5MW	32733		
R-30685H	30685	LASER HEAD FOR R-32172, 3.39UM, 2.0MW, POL	39785	LHIP-0201-339	30545
R-30630H	30630	LASER HEAD FOR R-30990, 633NM, 5.0MW, RANDOM	39783	LHRR-0500	30560
R-30028H	30028	LASER HEAD FOR R-30025, 633NM, 1.5MW, POL, 9.5"	39783		39696
R-39697H	39697	LASER HEAD FOR R-31007, 633NM, 0.8MW, POL	39783		
R-39698H	39698	LASER HEAD FOR R-31008, 633NM, 0.5MW, RAN	39783		
R-30682H	30682	LASER HEAD FOR R-30968, 543NM, 0.5MW, POL	39783	LHGP-0051	30525
R-30624H	30624	LASER HEAD FOR R-30993, 633NM, 12.0MW, POL	39785	LHRP-1201	30556
R-32656H	32656	LASER HEAD FOR R-33361, 543NM, 1.5MW, POL	39784	LHGP-0151	30528
R-30605H	30605	LASER HEAD FOR R-30967, 543NM, 0.5MW, RAN	39783	LHGR-0050	30529
R-30629H	30629	LASER HEAD FOR R-30988, 633NM, 2.0MW, RAN	39783	LHRR-0200	30559
R-30627H	30627	LASER HEAD FOR R-31425, 633NM, 35MW, POL, 115V	30582	LSRP-3501	39699
R-30612H	30612	LASER HEAD FOR R-33141, 1.52UM, 1.0MW, POL	39785	LHIP-0101-152	30542
R-30633H	30633	LASER HEAD FOR R-30992, 633NM, 12.0MW, RANDOM	39785	LHRR-1200	30564
R-30627H	30627	LASER HEAD FOR R-32413, 633NM, 35MW, POL, 230V	30584	LSRP-3501	39699
R-30639H	30639	LASER HEAD FOR R-39582, 594NM, 2.0MW, POL	39783	LHYP-0201	30572
R-30635H	30635	LASER HEAD FOR R-39635, 633NM, 17.0MW, RANDOM	39786	LHRR-1700	30567
R-39728H	39728	LASER HEAD FOR R-39727, 633NM, STBLZD, >1.2MW	32733		
R-30526H	30526	LASER HEAD FOR R-39581, 543NM, 1.0MW, POL	39784	LHGP-0101	
R-30571H	30571	LASER HEAD FOR R-40094, 594NM, 1.0MW, POL	39783		
R-30532H	30532	LASER HEAD FOR R-39568, 543NM, 1.0MW, RAN	39783		

**Power Supplies**

<b>Newport Part No.</b>	<b>REO Part No.</b>	<b>Description</b>
R-39783PS	39783	POWER SUPPLY, HENE, 1.5-2.3 KV
R-39784PS	39784	POWER SUPPLY, HENE, 2.5-3.2 KV
R-39785PS	39785	POWER SUPPLY, HENE, 2.7-3.3 KV
R-39786PS	39786	POWER SUPPLY, HENE, 3.2-3.8 KV
R-32733PS	32733	POWER SUPPLY, CONTROL BOX, STABILIZED R-32734
R-30582PS	30582	POWER SUPPLY, 115V, R-31425
R-30584PS	30584	POWER SUPPLY, 230V, R-32413
R-30651PS	30651	Power Supply, OEM, Voltex, G-22-HT
R-30649PS	30649	Power Supply, OEM, Volt, #DG-22-00
R-30655PS	30655	Power Supply, OEM Brick