



| Model | Thread | Angular Range $\pm\alpha$ (°) | Dimensions [in. (mm)] | | | | | | | | | | | |
|---------|--------|----------------------------------|-----------------------|-----------|------------|-------------|-----------|-------------|----------|-----------|-------------|-----------|-------------|-----------|
| | | | A | B | C1 | C2 | D | E | F | G | H | J | CA* | RB* |
| SL25.4 | M3 | 3 | 3.50 (89) | 1.61 (41) | 1.97 (50) | 1.28 (32.5) | 0.63 (16) | 0.49 (12.5) | 0.35 (9) | 0.79 (20) | 0.55 (14) | 0.83 (21) | 0.45 (11.5) | 0.35 (9) |
| SL50 | M5 | 2 | 4.88 (124) | 2.44 (62) | 2.95 (75) | 2.11 (53.5) | 0.63 (16) | 0.49 (12.5) | 0.35 (9) | 1.89 (48) | 0.53 (13.5) | 1.8 (46) | 1.16 (29.5) | 1.02 (26) |
| SL51 | M5 | 2 | 4.88 (124) | 2.44 (62) | 2.95 (75) | 2.11 (53.5) | 0.63 (16) | 0.49 (12.5) | 0.35 (9) | 1.89 (48) | 0.53 (13.5) | 1.8 (46) | 1.15 (29.3) | 0.98 (25) |
| SL76.2 | M5 | 2 | 5.91 (150) | 2.68 (68) | 2.95 (75) | 2.34 (59.5) | 0.63 (16) | 0.49 (12.5) | 0.35 (9) | 1.89 (48) | - | 2.7 (70) | 1.85 (47) | 1.53 (39) |
| SL101.6 | M5 | 2 | 6.69 (170) | 3.07 (78) | 3.94 (100) | 2.74 (69.5) | 0.63 (16) | 0.53 (13.5) | 0.35 (9) | 1.89 (48) | - | 3.6 (93) | 2.36 (60) | 2.20 (56) |

* CA is Clear Aperture, RB is Reflected Beam, TB is Transmitted Beam

