



Model	Thread	Diameter [in. (mm)]			Dimensions [in. (mm)]			
	A	B	C	D	E	F	G	H
FH-05R	0.546-32	0.52 (13.2)	0.437 (11.1)	0.75 (19.1)	0.50 (12.7)	1.00 (25.4)	0.30 (7.6)	0.91 (23.0)
FH-1R	1.063-20	1.01 (25.7)	0.932 (23.7)	0.75 (19.1)	0.65 (16.5)	1.00 (25.4)	0.48 (12.2)	1.41 (35.8)
FH-2R	2.063-20	2.01 (51.1)	1.937 (49.2)	1.25 (31.8)	1.17 (29.7)	1.50 (38.1)	0.60 (15.2)	2.41 (61.2)