


DIFFRACTION GRATING SPECIFICATION SHEET

Catalog no.	53-*-426R	3/24/2021			
Grating Description	150 g/mm plane ruled reflection grating with 3.4° nominal blaze angle				
Master no.	1569				
Maximum Ruled Area:		groove length	154 mm		
		ruled width:	206 mm		
·		1	1		

Efficiency Curve	spectral order:	m = 1	polarization(s):	S and P
	Coating:	aluminum		
Remarks:				



1569-1-3-1, 150 g/mm, 800 nm, 3.4 deg., M=1, Cat# 53-*-426, Plane ruled, Max RA 154 x 206 mm

Note: The efficiency curve above is relative (not absolute) and was measured in an in-plane near Littrow configuration (unless otherwise indicated). Efficiency curves are only representative: actual efficiency may vary significantly depending on use geometry and measurement technique. This efficiency curve is for master 1569; two masters with the same catalog number may have different efficiency curves. The uncertainty band on the data in the above efficiency curve(s) is +/- three percentage points.

©2021 Newport Corporation All rights reserved.