


705 St. Paul Street Rochester, New York 14605 Telephone: (585) 248-4100 Fax: (585) 248-4111

E-mail: gratings@newport.com Web Site: https://www.gratinglab.com

DIFFRACTION GRATING SPECIFICATION SHEET

Catalog no.	53-*-770R		3/24/2021	
Grating Description	300 g/mm plane ruled reflection grating with 17.5° nominal blaze angle			
Master no.	0900			
Maximum Ruled Area:		groove length	102 mm	
		ruled width:	128 mm	

Efficiency Curve	spectral order:	m = 1	polarization(s):	S and P
	Coating:	aluminum		
Remarks:				



Note: The efficiency curve above is relative (not absolute) and was measured in an in-plane near Littrow configuration (unless otherwise indicated). Efficiency curves are only representative: actual efficiency may vary significantly depending on use geometry and measurement technique. This efficiency curve is for master 0900; two masters with the same catalog number may have different efficiency curves. The uncertainty band on the data in the above efficiency curve(s) is +/- three percentage points.