## **XPS-RLD**

Universal High-Performance 1-4 Axis Motion Controller and Driver

# ••mks

The XPS-RLD is a cost effective high-performance, easy to use, integrated motion controller/driver with highspeed communication through 10/100/1000 Base-T Ethernet, outstanding trajectory accuracy and powerful programming functionality. With its user-friendly web interface, it is easy to setup advanced trajectory and synchronization features to precisely control from the most basic to the most complex motion sequences. With advanced compensation algorithms in the servo loop for linear error, backlash, positioner error mapping (including XY and XYZ error mapping) positioning accuracy in the nanometer range can be achieved. It also has multiple digital and analog I/O's, triggers and supplemental encoder inputs that provide users with additional data acquisition, synchronization and control features that can improve the most demanding motion applications. The XPS controller is capable of driving up to 4 axes of most Newport positioners using driver cards that slide through the back of the chassis. These factory-tested drives are powered by a dedicated internal 300 W power supply, which is independent of the controller power supply. When used with Newport ESP stages, the configuration of the driver cards and the associated stage is easy using the auto-configuration utility software. Advanced users can also manually develop their own configuration files optimized for specific applications.

#### **Product Features**

- Up to 4 axes universal motion controller
- High-speed 10/100/1000 Base-T Ethernet TCP/ IP communication
- User-friendly web interface w/ multi user capabilities
- Real-time Processing and Multitasking
- Wide variety of motion modes from basic to complex PVT trajectories
- 10 kHz servo loop with advanced variable PID's

#### **Applications / Benefits**

 Supports quadrature incremental and Sin/Cos analog encoders

Newport

- Low noise encoder interpolation for nanometer MIM
- Extensive Analog and Digital I/O Capability
- High speed Position Compare Output (PCO) for up to 2-Axis
- ESP Plug-and-Play Compatibility

The new XPS-DRV11 universal driver module allows the XPS-RLD to drive any bipolar stepper, DC brush, and direct drive motor stages. Although the XPS-RLD is backward compatible with the older DRV0x cards, it is highly recommended to use the XPS-DRV11. By using the XPS-DRV00P pass-through drive module, the XPS can external amplifiers/drives through step/direction or analog signals to operate third party motors. XPS-DRVP1 can control Newport's Nano positioning piezo stack devices. All driver modules must be purchased separately. For more information please visit our drive module webpage: https://www.newport.com/f/xps-controller-driver-modules



XPS-RLD driver cards easily slide in

#### **Order Information**

XPS-RLDM	1-axis Cost effective, High performance Universal Motion Controller
XPS-RLD2	2-axis Cost effective, High performance Universal Motion Controller
XPS-RLD4	4-axis Cost effective, High performance Universal Motion Controller

#### Accessories

XPS-RLD-R

XPS-RLD Motion Controller Rack Mounting Kit





### **Specifications**

Number of Axes	<ul> <li>1 to 4 axes of stepper, DC brush, DC brushless, linear or piezo motors using internal drives: XPS-RLDM: 1-axis; XPS-RLD2: 2-axis; XPS-RLD4: 4-axis.</li> </ul>
Communication Interfaces	Internet protocol TCP/IP
	One Ethernet 10/100/1000 Base-T (RJ45 connector) with fixed IP address and DHCP server for local communication
	One Ethernet 10/100/1000 Base-T (RJ45 connector) for networking, dynamic addressing with DHCP and DNS
	Typically, 0.3 ms from sending a tell position command to receiving the answer
Firmware Features	Powerful and intuitive, object-oriented command language
	Native user-defined units (no need to program in encoder counts)
	Real-time execution of custom tasks using TCL scripts
	Multi-user capability
	Concept of sockets for parallel processes
	Time & position spaced trigger output pulses, 0.05 Hz to 20 MHz, 5 ns accuracy
	Data gathering at servo rate, up to 1,000,000 data entries (depending on servo rate)
	Auto-configuration, auto-tuning and auto-scaling
Motion	Jogging mode including on-the-fly changes of speed and acceleration
	Synchronized point-to-point
	Spindle motion (continuous motion with periodic position reset)
	• Line-arc mode (linear and circular interpolation incl. continuous path contouring)
	Splines (Catmull-Rom type)
	• PT trajectories (continuous, multidimensional motion path)
	• PVT trajectories (complex trajectory based on position, velocity and time coordinates)
	Analog tracking (using analog input as position or velocity command)
	Mactor clave including single master multiple slaves and custom dear ratio
Compensation	
Carrie Data	All corrections are taken into account on the servo loop
Servo Rate	
I/O	• 8 FIL inputs and 8 FIL outputs (open collector)
	• 2 synch, analog inputs ±10 V, 12 bits
	• 2 synch. analog outputs ±10 V, 12 bits
Control Loop	Open loop, PI position, PIDFF velocity, PIDFF acceleration, PIDDualFF voltage
	Variable PID's (PID values depending on distance to target position)
	Derivative cut-off filter; 2 user-defined notch filters
Trigger In	Hardware latch of all positions and all analog I/O's (on servo rate)
	< 50 ns latency on positions
	<125 µs time jitter on analog I/O's
Trigger Out	One high-speed position compare output only for axes 1 and 2 that can be either configured for position synchronized pulses or for time synchronized pulses: 5 ns accuracy, <700 ns latency (from real stage position to pulse generation), 5 MHz max frequency
	Position Compare Output (PCO):
	- interpolation ×256
	- error compensated (except XY or XYZ mapping)
Dedicated Inputs Per Axis	• RS-422 differential inputs for A. B and I. Max. 25 MHz, over-velocity and guadrature error detection
	• 1 Vpp analog encoder input up to ×65536 interpolation used for servo; amplitude, phase and offset correction and synchronization
	Low noise encoder interpolator board for nanometer MIM
	Forward and reverse limit, home, error input
Dedicated Outputs Per Axis (when using external drives)	• 2 channel 16-bit, ±10 V D/A
	Drive enable, error output
Drive Capability	• 300 W (@ 230 VAC) total available power
AC Power Requirements	• 100–240 VAC 60/50 Hz 9.5 A– 5.5 A





www.MKSINST.com DS-062002 XPS-RLD ©2020 MKS Instruments, Inc.Specifications are subject to change without notice. MKS products provided subject to the US Export Regulations. Export, re-export, diversion or transfer contrary to US law (and local country law) is prohibited. mksinst<sup>™</sup> and DELTA<sup>™</sup> are trademarks of MKS Instruments, Inc., Andover, MA. Swagelok<sup>®</sup> and VCR<sup>®</sup> are registered trademarks of Swagelok Marketing Co., Solon, OH. DeviceNet<sup>™</sup> is a trademark of the Open DeviceNet Vendor Association, Coral Springs, FL. Inconel<sup>®</sup> is a registered trademark of Inco Alloy International, Huntington, WV. Hastelloy<sup>®</sup> is a registered trademark of Haynes International, Kokomo, IN. EtherCAT<sup>®</sup> is a registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany.