

LMA-PM-15

Single mode 15 μm polarization-maintaining fiber



- Low loss fiber from 600 to 1700 nm
- Single mode at all wavelengths
- Polarization Maintaining
- Radiation hard pure silica fiber
- Wavelength independent MFD

This polarization-maintaining single-mode fiber is optimized to exhibit low loss from 600 nm to 1700 nm while keeping an almost constant mode field diameter.

The fiber is endlessly single-mode (i.e. it has no higher order mode cut-off) and delivers pristine mode quality at all wavelengths.

This product is also available in a non polarization-maintaining version as the LMA-15

Optical properties	
Single mode cut-off wavelength*	None
Attenuation @ 780 nm	< 25 dB/km
Attenuation @ 1064 nm	< 10 dB/km
Attenuation @ 1550 nm	< 5 dB/km
Mode field diameter @ 780 nm ($1/e^2$)	$12.4 \pm 0.5 \mu\text{m}$
Mode field diameter @ 1064 nm ($1/e^2$)	$12.6 \pm 0.5 \mu\text{m}$
NA @ 1064 nm (5%)	0.09 ± 0.02
Birefringence Δn @ 1064 nm	$1.3 \cdot 10^{-4}$
Polarization Extinction Ratio**	> 18 dB


Physical properties	
Core diameter	$14.8 \pm 0.5 \mu\text{m}$
Outer cladding diameter, OD	$230 \pm 5 \mu\text{m}$
Coating diameter	$350 \pm 10 \mu\text{m}$
Core and cladding material	Pure silica
Coating material, single layer	Acrylate
Coating concentricity	< 10 μm
Proof test level	0.33 %

Standard interfacing options	
FC/PC PM connector	0.0 ± 0.5 deg angle
FC/APC PMconnector	8.0 ± 0.5 deg angle
SMA 905	0.0 or 5.0 ± 0.5 deg angle
Collapse and cleave	0.0 ± 0.5 deg angle

All interfaces are provided with a $150 \pm 25 \mu\text{m}$ sealing length of the PCF structure. PM connectors are keyed to the slow axis. Please contact us for other custom interfacing options.

* TIA-455-80-C standard


** AKA PXtalk on a 2 m sample




Applications

- Single-mode PM short wavelength delivery
- Multi-wavelength transmission
- Mode filtering
- Single-mode PM pigtailing
- Short pulse delivery

Typical spectral attenuation and dispersion



Typical spectral NA and MFD



LMA-PM-15-111222