



Model	Thread	Diameter [in. (mm)]		D	E	F	G
	A	B min.	C				
LH-0.25	0.281-32	0.247 (6.3)	0.187 (4.7)	0.187 (4.7)	1.000 (25.4)	1.000 (25.4)	0.750 (19.1)
LH-0.5	0.546-32	0.512 (13.0)	0.437 (11.1)	0.398 (10.1)	1.000 (25.4)	1.000 (25.4)	0.750 (19.1)
LH-1	1.063-20	1.008 (25.6)	0.932 (23.7)	0.755 (19.2)	1.000 (25.4)	1.000 (25.4)	0.750 (19.1)
LH-1.5	1.563-20	1.509 (38.3)	1.407 (35.7)	1.180 (30.0)	1.500 (38.1)	1.500 (38.1)	1.250 (31.8)
LH-2	2.063-20	2.008 (51.0)	1.937 (49.2)	1.690 (42.9)	1.500 (38.1)	1.500 (38.1)	1.250 (31.8)
LH-OBJ	0.800-36	0.770 (19.6)	0.777 (19.7)		1.000 (25.4)	1.000 (25.4)	0.750 (19.1)

Model	H	I	J	K	L	M	N
LH-0.25	2.000 (50.8)	0.625 (15.9)	0.500 (12.7)	0.250 (6.4)	0.375 (9.5)	0.187 (4.7)	0.093 (2.4)
LH-0.5	2.000 (50.8)	0.907 (23.0)	0.500 (12.7)	0.250 (6.4)	0.375 (9.5)	0.187 (4.7)	0.093 (2.4)
LH-1	2.000 (50.8)	1.407 (35.7)	0.500 (12.7)	0.250 (6.4)	0.500 (12.7)	0.250 (6.4)	0.127 (3.2)
LH-1.5	3.000 (76.2)	1.907 (48.4)	0.500 (12.7)	0.250 (6.4)	0.500 (12.7)	0.250 (6.4)	0.127 (3.2)
LH-2	3.000 (76.2)	2.407 (61.1)	0.500 (12.7)	0.250 (6.4)	0.500 (12.7)	0.250 (6.4)	0.127 (3.2)
LH-OBJ	2.000 (50.8)	1.407 (35.7)	0.500 (12.7)	0.250 (6.4)	0.500 (12.7)	0.250 (6.4)	