



Model	A	B	THDC	D	E	F	G	H	J	T
SLM-12A	6.88 in.	6.00 in.	0.500-13	0.53 in.	0.29 in.	6.74 in.	3.50 in.	3.00 in.	0.56 in.	0.125 in.
SLM-192A	24.0 in.	20.0 in.	1.000-14	0.88 in.	0.81 in.	24.00 in.	3.50 in.	15.75 in.	0.56 in.	0.250 in.
SLM-1A	3.0 in.	2.38 in.	0.375-16	0.47 in.	0.28 in.	2.88 in.	2.5 in.	1.0 in.	0.5 in.	0.125 in.
SLM-24A	10.0 in.	8.50 in.	0.625-11	0.75 in.	0.56 in.	9.66 in.	3.50 in.	4.75 in.	0.56 in.	0.188 in.
SLM-3A	4.19 in.	3.50 in.	0.500-13	0.53 in.	0.28 in.	4.14 in.	2.45 in.	1.75 in.	0.54 in.	0.125 in.
SLM-48A	13.5 in.	12.0 in.	0.625-11	0.75 in.	0.56 in.	13.31 in.	3.50 in.	7.5 in.	0.56 in.	0.188 in.
SLM-6A	5.12 in.	4.25 in.	0.500-13	0.53 in.	0.29 in.	4.99 in.	3.50 in.	2.13 in.	0.56 in.	0.125 in.
SLM-96A	18.5 in.	16.0 in.	1.000-14	0.88 in.	0.81 in.	18.44 in.	3.50 in.	10.5 in.	0.56 in.,	0.250 in.