




Model	Diameter	Thickness	CA
10QM20EM.15	25.4 mm	6.35 mm	20.32 mm
10QM20EM.25	25.4 mm	6.35 mm	20.32 mm
10QM20EM.35	25.4 mm	6.35 mm	20.32 mm
10QM20HDM.10	25.4 mm	6.35 mm	20.32 mm
10QM20HM.30	25.4 mm	6.35 mm	20.32 mm
10QM20HM.35	25.4 mm	6.35 mm	20.32 mm
10QM20HM.40	25.4 mm	6.35 mm	20.32 mm
10QM20HM.75	25.4 mm	6.35 mm	20.32 mm
10QM20HDM.15	25.4 mm	6.35 mm	20.32 mm
10QM20HM.10	25.4 mm	6.35 mm	20.32 mm
10QM20HM.15	25.4 mm	6.35 mm	20.32 mm
10QM20HM.15-G	25.4 mm	6.35 mm	20.32 mm
10QM20HM.35-G	25.4 mm	6.35 mm	20.32 mm
10QM20HM.45	25.4 mm	6.35 mm	20.32 mm
10QM20HM.45-G	25.4 mm	6.35 mm	20.32 mm
10QM20HM.75-G	25.4 mm	6.35 mm	20.32 mm

Model	Diameter	Thickness	CA
20QM20EM.15	50.8 mm	9.525 mm	40.64 mm
20QM20EM.25	50.8 mm	9.525 mm	40.64 mm
20QM20EM.35	50.8 mm	9.525 mm	40.64 mm
20QM20HM.15	50.8 mm	9.525 mm	40.64 mm
20QM20HM.35	50.8 mm	9.525 mm	40.64 mm
20QM20HM.45	50.8 mm	9.525 mm	40.64 mm
20QM20HM.75	50.8 mm	9.525 mm	40.64 mm
20QM20HM.10	50.8 mm	9.525 mm	40.64 mm
20QM20HM.15-G	50.8 mm	9.525 mm	40.64 mm
20QM20HM.35-G	50.8 mm	9.525 mm	40.64 mm
20QM20HM.45-G	50.8 mm	9.525 mm	40.64 mm
20QM20HM.75-G	50.8 mm	9.525 mm	40.64 mm