



Model	Outer Diameter (mm)	Thickness (mm)	Clear Aperture (mm)	Radius of Curvature (mm)
10DC50AL.2	25.4	6.35	20.32	25
10DC50ER.1	25.4	6.35	20.32	25
10DC50ER.2	25.4	6.35	20.32	25
10DC100AL.2	25.4	6.35	20.32	50
10DC100ER.1	25.4	6.35	20.32	50
10DC100ER.2	25.4	6.35	20.32	50
10DC200AL.2	25.4	6.35	20.32	100
10DC200ER.1	25.4	6.35	20.32	100
10DC200ER.2	25.4	6.35	20.32	100
10DC500AL.2	25.4	6.35	20.32	250
10DC500ER.1	25.4	6.35	20.32	250
10DC500ER.2	25.4	6.35	20.32	250
10DC1000AL.2	25.4	6.35	20.32	500
10DC1000ER.1	25.4	6.35	20.32	500
10DC1000ER.2	25.4	6.35	20.32	500