APEX2

Oriel® Illumination Systems



Quick Start Guide



TABLE OF CONTENTS

1	GENER	AL INFORMATION	
	1.1	SYMBOLS AND DEFINITIONS	
	1.2	GENERAL WARNINGS	
	1.3	ELECTRICAL HAZARDS	
	1.4	FIRE HAZARDS	
	1.5	LAMP HANDLING	
2		DUCTION	
3	SYSTE	M SETUP	10
	3.1	ITEMS INCLUDED WITH SYSTEM	
	3.2	UNPACKING	
	3.3	CHOOSING A LOCATION	
	3.4 3.5	ASSEMBLYLAMP INSTALLATION	11
	3.5 3.6	ELECTRICAL CONNECTION	
	3.7	LAMP INTENSITY ADJUSTMENT (APEX2-QTH ONLY)	
4		OLLING THE APEX2 FILTER WHEEL	
		FEATURES	
5	5.1	FLATURESFILTER WHEEL OVERVIEW	
	5.1 5.2	SHUTTER	
	5.3	ADJUSTABLE COLLIMATING LENS	26
	5.4	MATING FLANGE OPTIONS	
6	FILTER	INSTALLATION	
7	MAINTE	NANCE	30
•	7.1	LAMP REPLACEMENT	
	7.2	CLEANING	
	7.3	LAMP CARE AND HANDLING	30
	7.4	FUSE REPLACEMENT	30
8	SPECIF	ICATIONS	31
	8.1	APEX2 ILLUMINATOR	
	8.2	UNIVERSAL FILTER WHEEL UTILITY SOFTWARE	
9	EU DEC	CLARATION OF CONFORMITY	33
10	WARRA	NTY AND SERVICE	34
	10.1	CONTACTING ORIEL INSTRUMENTS	34
		REQUEST FOR ASSISTANCE / SERVICE	
		REPAIR SERVICE	
		NON-WARRANTY REPAIR	
		WARRANTY REPAIR	
	10.6	LOANER / DEMO MATERIAL	37
116.	T OE FI	CURES	
LIO	i UF FI	GURES	
Figur	re 1· AP	EX2-XE Lamp Spectra	۶
Figur	e 2: AP	EX2-QTH Lamp Spectra	9
		v the APEX2 unit arrives in its packaging	
		nt lens assembly and integrated light source	
Figur	re 7: Fem	hale flange of the integrated light source unit (left) and installed front lens assembly (right)	13
		alled front lens assembly with Collimating Lens Adjustment Ring set screw oriented vertical	
for ea	asy acce	ssibility	13

Figure 3: I	Remove Top Cover Screw	.14
Figure 4: I	Remove Housing Cover	.15
Figure 5: I	Remove Lamp Cable Holder	.15
Figure 6: I	Move Lamp Holder Wires	.16
Figure 7: I	Unfasten Power Supply Cable	.16
Figure 8: I	nsert Lamp	.17
Figure 9: I	Lamp Ellipse Positioning Groove	.17
Figure 10:	Secure Lamp	. 18
Figure 11:	Connect Lamp Wiring	.18
Figure 12:	Re-attach Lamp Cable Holder	.19
Figure 13:	Completed Lamp Installation	.19
Figure 14:	Safety Interlock	.20
Figure 15:	Cover Re-installed	.20
Figure 16:	APEX2 Power Connection	.22
Figure 17:	Lamp Intensity Adjustment Settings	.23
Figure 18:	Filter wheel pushbutton	.24
Figure 19:	Shutter Knob	. 25
Figure 20:	Collimating Lens Adjustment	.26
Figure 21:	Do Not Adjust Relay Lens	.26
Figure 22:	Oriel 1.5-Inch Series Flange	.27
Figure 23:	Removing the Front Panel of the Filter Wheel	.28
Figure 24:	Filter Wrench Removing Retaining Ring	. 29
	Installed Filters	
Figure 26:	Fuse Compartment	.30
-		

1 GENERAL INFORMATION

Thank you for your purchase of this APEX2 illumination system from Oriel Instruments.

Please carefully read the following important safety precautions prior to unpacking and operating this equipment. In addition, please read the complete User's Manual for additional important notes and cautionary statements regarding the use and operation of the system.

1.1 SYMBOLS AND DEFINITIONS

\triangle	WARNING Situation has the potential to cause bodily harm or death.
\triangle	CAUTION Situation has the potential to cause damage to property or equipment.
<u>A</u>	ELECTRICAL SHOCK HAZARD Hazard arising from dangerous voltage. Any mishandling could result in irreparable damage to the equipment, and personal injury or death.
CE	EUROPEAN UNION CE MARK The presence of the CE Mark on Newport Corporation equipment means that it has been designed, tested and certified as complying with all applicable European Union (CE) regulations and recommendations.
NOTE:	Additional important information the user or operator should consider.

Please read <u>all</u> instructions that were provided prior to operation of the system.

If there are any questions, please contact Oriel Instruments or the representative through whom the system was purchased.

1.2 GENERAL WARNINGS

- Read all warnings and operating instructions for this system prior to setup and use.
- Do not use this equipment in or near water.
- To prevent damage to the equipment, read the instructions in the equipment manual for proper input voltage.
- This equipment is grounded through the grounding conductor of the power cord.
- Route the power cord and other cables so they are not likely to be damaged.
- Disconnect power before cleaning the equipment.
- Do not use liquid or aerosol cleaners; use only a dry lint-free cloth.
- Lock out all electrical power sources before servicing the equipment.
- To avoid explosion, do not operate this equipment in an explosive atmosphere.
- Qualified service personnel should perform safety checks after any service.
- If this equipment is used in a manner not specified in this manual, the protection provided by this equipment may be impaired.
- To prevent damage to equipment when replacing fuses, locate and correct the problem that caused the fuse to blow before re-applying power.
- Do not block ventilation openings.
- Do not position this product in such a manner that would make it difficult to disconnect the power cord.
- Use only the specified replacement lamp.
- This product should only be powered as described in the manual.
- Do not remove the cover for normal usage.

1.3 ELECTRICAL HAZARDS

Make all connections to or from the power supply with the power off.

Do not use the power supply without its cover in place. Lethal voltages are present inside.

1.4 FIRE HAZARDS

Lamps are extremely hot during operation, and for several minutes after being shut off. Keep flammable objects away from the lamp and lamp housing.

Newport Research (fan-cooled) Housings are equipped with a condenser lens. The re-focused output of this lens can cause ignition of flammable targets including but not limited to walls, certain chemicals.

To avoid fire hazard, use only the specified fuses with the correct type number, voltage and current ratings as referenced in the appropriate locations in the service instructions or on the equipment. Only qualified service personnel should replace fuses.

1.5 LAMP HANDLING

Read all information and warnings provided with lamp.

The Xenon arc lamp used in the APEX2-XE is filled with rare gas at high pressure, presenting the danger of lamp explosion due to mechanical failure. This is particularly true when the lamp is operating, as the internal pressure can reach tens of atmospheres. Thermal strains can also cause the lamp to explode under certain conditions.

Never touch a lamp's glass envelope or the reflector's inner surface with bare fingers or other contaminates. Skin oil or other substances can burn into the lamp envelope during operation and negatively affect the lamp's performance and lifetime.

Always wear appropriate powder free gloves and impact-resistant goggles when handling any lamp. Avoid any mechanical strain during handling. Do not operate the lamp without all housing panels in place.

Lamps become very hot after only a few minutes of operation (up to 150°C) and remain quite hot for at least 10 to 15 minutes after being turned off.

2 INTRODUCTION

The APEX2 illumination systems are designed to be compact, economical, fully integrated solutions suitable for a wide variety of applications. The APEX2 is a plug and play light source producing a collimated 1.3 inch (33 mm) diameter output beam. Simply install the lamp, connect the power cord and switch on the power – then the system is ready for use.

The systems are available with either a Xenon or Quartz Tungsten Halogen (QTH) lamp. Lamp replacement is easy – no alignment is needed. The lamp operates with a built-in power supply, so no current or power presets or adjustments are required. The APEX2 is designed with an ellipsoidal reflector, capturing additional light to increase optical throughput.

The APEX2 is designed to be quick and easy to set up. Mounting feet help with handling and leveling the illuminator. The mounting feet are removable, so the illuminator may be permanently mounted to an optical table if desired. The APEX2 comes preassembled on a plate with mounting holes for securing the illuminator to an inch or metric optical table / breadboard.

The light source is coupled to a filter wheel, where up to six neutral density or ordering sorting filters may be installed. A large, easy to read digital display indicates which filter is in the light path. Filters are sold separately, as their specifications are application-dependent.

The filters may be selected using a variety of methods, including manual control and software. For those who wish to create their own programs, low level commands may be sent to the system via USB connection from a personal computer (PC).

The APEX2 includes a manually operated shutter. It is important that the lamp is warmed up and stabilized when using the system. When the lamp is not needed, it can remain on (and therefore warmed up) by closing off the light path.

NOTE: Always allow the lamp to warm up for at least 30 minutes prior to beginning work.

The output flange of the APEX2 is compatible with the 1.5-inch Oriel flanging system. The collimated output may be coupled to a wide variety of items such as a beam turner, focusing optics, fiber optic cable adapter or detector.

Compatible instruments:

- Cornerstone 130 Monochromator
- Cornerstone 260 Monochromator
- MS260i Spectrograph
- MS257 Monochromator
- MS257 Spectrograph

NOTE:

In this user's manual, the term "monochromator" is used throughout the text. The APEX2 may be operated with both monochromators and spectrographs.




Figure 1: APEX2-XE Lamp Spectra




Figure 2: APEX2-QTH Lamp Spectra

3 SYSTEM SETUP

3.1 ITEMS INCLUDED WITH SYSTEM

Oriel Instruments provides a pre-aligned light source and filter wheel installed on a mounting plate. In addition, the system includes:

- 100 W Xe or QTH Lamp
- USB stick preloaded with Universal Filter Wheel Utility Software, User's Manual, and this Quick Start Guide
- Filter wrench
- 1/16 hex wrench
- US AC power cord
- EU AC power cord
- 74010-1020 Filter wheel cable assembly
- 2 pcs 0.8 A, 250 V 5 x 20 m fuse
- 4 pcs Mounting feet

3.2 UNPACKING

Remove all items from the shipping containers and verify each item is accounted for. The system is carefully packaged to minimize the possibility of damage during shipment. Inspect the shipping boxes for external signs of damage or mishandling. Inspect the contents for damage.

If any item is missing or damaged, immediately contact Oriel Instruments or the Newport representative from whom the system was purchased.

It is suggested to save the packaging material and shipping container, in case the equipment needs to be relocated at a future date.



WARNING

Do not attempt to operate this equipment if there is evidence of shipping damage or there is suspicion that the equipment will not operate correctly. Damaged equipment may present hazards.

3.3 CHOOSING A LOCATION

Choose an installation location where the power requirements can be met for the system. Be sure power is not applied to the system until the setup has been completed.


The environment should be that of a typical laboratory atmosphere, without excessive humidity and contaminants in the air. Do not allow the ventilation holes on the illuminator or its computer to be blocked. Air should be able to circulate freely around the system.

Carry the instrument by its base plate. When the system is placed in its final location, check to ensure that none of the pre-assembled items have become loose during transportation and handling.

3.4 ASSEMBLY

To ensure the front lens assembly and integrated light source components of the APEX2 unit remain undamaged during shipping, these two components are packaged as separate items within the protective foam the APEX2 is shipped in. Some minor assembly is required before the lamp can be installed.

The top piece of foam houses the miscellaneous accessories included with the APEX2 (AC power cords, etc.), front lens assembly, and Xe/QTH lamp. Remove the protective foam placed over the front lens assembly, remove the front lens assembly from its protective packaging, and set the front lens assembly aside.





Front Lens Assembly

Figure 3: How the APEX2 unit arrives in its packaging

 Remove the top piece of foam to reveal the integrated arc lamp/QTH source. Remove the integrated light source from the protective foam. The two items as shown in Figure 4 are now ready for assembly.




Figure 4: Front lens assembly and integrated light source

2. Insert the male flange of the front lens assembly into the female flange of filter wheel of the integrated light source unit as shown in Figure 5. Install with the set screw of the blue Collimating Lens Adjustment Ring oriented upright as shown in Figure 6. This will make the set screw easily accessible for future adjustment. When the front lens assembly is installed in an optimal orientation, secure the assembly in place with the three 6-32 x 3/16 socket set cone point set screws provided.




Figure 5: Female flange of the integrated light source unit (left) and installed front lens assembly (right)



Figure 6: Installed front lens assembly with Collimating Lens Adjustment Ring set screw oriented vertically for easy accessibility

The APEX2 is now ready for lamp installation.

3.5 LAMP INSTALLATION

Before plugging in the power cord and powering up the APEX2, the lamp must be installed. The lamp is shipped in its own box to prevent damage during transportation. It is suggested to keep this box, as it can be utilized if moving or transporting the APEX2 in the future. Never move the APEX2 while the lamp is installed. Damage to the lamp or system may result.



ELECTRICAL SHOCK HAZARD

Do not open the APEX2 cover and attempt to work inside without first turning the instrument off and disconnecting the power cord from the AC mains. Failure to follow this warning can result in severe injury or death.



WARNING

When installing the lamp, it is required to:

- Wear eye protection.
- Wear powder-free gloves.
- Make sure the power is turned off.
- 1. Using a Phillips head screwdriver, remove the (4) screws holding the top cover of the housing and set aside. Refer to Figure 7.



Figure 7: Remove Top Cover Screw

2. Remove the top cover and set aside as shown in Figure 8.



Figure 8: Remove Housing Cover

3. Loosen and remove the knurled thumb screw as shown in Figure 9. Remove the lamp cable holder plate and set aside with the thumb screw.





Figure 9: Remove Lamp Cable Holder

4. Press the lamp holder wires toward each other and then pull them toward the rear of the APEX2 unit. This is demonstrated in Figure 10.






Figure 10: Move Lamp Holder Wires

5. The power supply cable shown in Figure 11 is secured for transportation. Unfasten it and let it hang to the side for now.




Figure 11: Unfasten Power Supply Cable

6. Insert the lamp as shown in Figure 12. The outer edge of the elliptical reflector must fit into the groove shown in Figure 13.



CAUTION

Always wear powder-free gloves or finger cots when handling the lamp. Handle the lamp from the outside of the reflector. Making contact with the lamp or reflector may cause permanent damage.



Figure 12: Insert Lamp




Figure 13: Lamp Ellipse Positioning Groove

7. Secure the lamp in place by returning the lamp holder wires to their original location per Figure 14.




Figure 14: Secure Lamp

8. Connect the lamp wiring to the power supply cable. The connectors are designed so that they cannot be connected incorrectly, so there is no need to be concerned with lamp polarity. See Figure 15.



Figure 15: Connect Lamp Wiring

9. Re-attach the lamp cable holder which was set aside earlier by tightening the thumb screw as shown in Figure 16. The completed lamp installation is shown in Figure 17.




Figure 16: Re-attach Lamp Cable Holder




Figure 17: Completed Lamp Installation

10. Re-install the cover, ensuring that the top cover's safety interlock lines up with its slot in the bottom portion of the housing as shown in Figure 18.



Figure 18: Safety Interlock

11. Using a Phillips head screwdriver, re-install the (4) screws to secure the top cover of the housing. Do not leave out any screws.



Figure 19: Cover Re-installed

3.6 ELECTRICAL CONNECTION

Before powering up the system for the first time, it is suggested to have a qualified electrician verify the wall socket to be used with the APEX2 meets the requirements for operation as noted.

The line voltage requirements for the APEX2 are as follows:

100 to 120 VAC, 50-60 Hz 200 to 240 VAC, 50-60 Hz

ELECTRICAL SHOCK HAZARDS



To avoid electric shock, connect the instrument to a properly earth-grounded, 3-prong receptacle only. Failure to observe this precaution can result in severe injury or death.

Never attempt to open the lamp power supply or monochromator power adapter. These items do not contain any user serviceable parts. Failure to follow this warning can result in severe injury or death.

The APEX2 illumination systems conform to CE standards for both safety and EMC. During normal use, this equipment will not pose any electrical hazards to the user. Read all warnings before installing or operating this system. Never open the APEX2 cover and attempt to work inside without first turning the instrument off and disconnecting the power cord from the AC mains.



CAUTION

Do not turn on the APEX2 until all connections have been made to the monochromator, computer, hand controller and/or external 5 VDC source. Refer to Section 4 for information on various methods and required connections to control the APEX2.

If there are any questions or concerns, contact Oriel Instruments or the regional sales representative for Newport.



WARNING

When the power switch is turned on, the lamp will begin emitting light immediately. Do not turn on the APEX2 until the output flange is directed in such a way that people, animals and equipment will not be harmed by the light.

A dedicated power line or line isolation may be required in certain locations, as the electronics contained in the instrument are sensitive to static electricity and radiated electromagnetic fields. Operation of the system near intense pulsed sources (lasers, Xenon flash lamps, etc.) may compromise performance.

Before making any electrical connections, verify the power switches are in the OFF position for the APEX2 and monochromator, if being used.

Connect the power cord to the back of the APEX2 before to plugging it into an AC electrical outlet.




Figure 20: APEX2 Power Connection

NOTE: Always allow the lamp to warm up for <u>at</u> <u>least</u> 30 minutes prior to beginning work.

3.7 LAMP INTENSITY ADJUSTMENT (APEX2-QTH ONLY)

The model APEX2-QTH allows for lamp intensity to be controlled by an external DC voltage source. External control is enabled by moving the toggle switch on the back panel to the **UP** position. When the toggle switch is in the **DOWN** position, the lamp will operate at its full power rating of 100 watts.

The BNC female connector on the back of the APEX2-QTH is used to connect a DC voltage source. The input voltage range is 0 to 5 VDC. 0 VDC corresponds to the lamp being off; 5 VDC allows the lamp to run at its maximum power of 100 watts.

NOTE:

In the event that the lamp is not operating and an external voltage source is not being applied, check the position of the toggle switch and ensure it is in the DOWN position.




Figure 21: Lamp Intensity Adjustment Settings

4 CONTROLLING THE APEX2 FILTER WHEEL

The APEX2 integrates a light source, filter wheel and power supply into a complete package. Power is supplied to both the lamp and the filter wheel. A large, easy to read digital display indicates which filter is active, i.e. which filter is in the light path. The digital display is positioned on the rear panel of the filter wheel assembly, so that it may be observed from a safe and convenient viewing angle not within the path of the output light.

The simplest method of controlling the filter wheel is by pressing the manual pushbutton located on the back of the filter wheel as shown in Figure 22. Pressing this button advances the filter by one position. Filter installation is covered in Section 6.




Figure 22: Filter wheel pushbutton

5 APEX2 FEATURES

The APEX2 provides a number of features into a convenient, compact illumination system. All features are integrated into the unit, to keep the system easy to transport, set up and operate.

5.1 FILTER WHEEL OVERVIEW

The motorized filter wheel holds up to six (6) filters. The MS257 monochromator was designed to work with filter wheels containing up to five (5) filters. When the MS257 is used with the APEX2, the first five filters will be selectable. When used alone or with other monochromators, all six (6) filter positions may be utilized. The active filter position changes at a rate of 1.7 seconds per filter.

5.2 SHUTTER

The integrated shutter is a very convenient feature which may be used to close off the light path while the lamp is warming up, or a change in setup is being performed. Frequently restarting the lamp may shorten the lamp's life and resets the warm-up time. If the lamp is not needed for a short amount of time, the shutter can simply be closed.

Turning the knob clockwise opens the shutter. Rotating the knob counterclockwise closes the shutter.




Figure 23: Shutter Knob

5.3 ADJUSTABLE COLLIMATING LENS

The collimating lens may be adjusted to optimize light coupling. Loosen the silver thumb screw shown in Figure 24. Turn the blue knob near the output flange to change the lens position. Be sure to tighten the locking screw when finished.

Note: under normal circumstances, this is the <u>only</u> lens which should be adjusted. Do not make any changes to the relay lens position, as its position was optimized before shipment.



Figure 24: Collimating Lens Adjustment



Figure 25: Do Not Adjust Relay Lens

5.4 MATING FLANGE OPTIONS

The APEX2 is designed with a standard Oriel 1.5-inch series mating flange, allowing it to be coupled to a variety of instruments and accessories. Items are connected to the mating flange by tightening three set screws, shown in Figure 26.




Figure 26: Oriel 1.5-Inch Series Flange

6 FILTER INSTALLATION

WARNING



When the light source is in use, the filter wheel and all other items in the optical path may become hot. Ensure items are cool before handing them.

Ensure the shutter is closed and the lamp is off whenever working in the filter wheel compartment.

Remove the front plate of the filter wheel assembly by unscrewing eight (8) flat head screws using a Phillips screwdriver. Refer to Figure 27.

Set all items aside, ensuring that no foreign matter can contaminate or damage the optics. Do not attempt to disconnect the output optics and flange from the front plate.



Figure 27: Removing the Front Panel of the Filter Wheel

Each filter position is labeled on the wheel. Remove the filter retaining ring using the filter wrench included with the system. Insert the filter and re-install the retaining ring. Always wear gloves or finger cots when handing optics. See Figure 28 and Figure 29.

For all filter positions which are not being utilized, ensure the retaining rings are snug so that they do not become loose and obstruct the filter wheel. Only then should the filter cover be re-installed.

Note: Always keep track of which filters are installed at each slot in the filter wheel. It is suggested to write down this information and update it whenever the configuration is changed. This is particularly helpful when multiple users will be operating the APEX2 system.



Figure 28: Filter Wrench Removing Retaining Ring



Figure 29: Installed Filters

7 MAINTENANCE

7.1 LAMP REPLACEMENT

The average life of each lamp type is noted below. Note that the lifetime of the lamp can be affected by the manner in which it is used. Frequent ignitions, contamination of the lamp envelope and an excessively hot operating environment all will lead to reduced lamp life.

To avoid system down time, consider purchasing a replacement lamp as the lamp nears the end of its useful life. Refer to the Section 3.5 of this manual for information on lamp installation.

APEX2 Model	<u>Lamp Type</u>	Lamp Model	Average Lifetime
APEX2-QTH	100 W QTH	6338	500 hours
APEX2-XE	100 W Xe	6252	1000 hours

7.2 CLEANING

Clean the exterior of the APEX2 when the illuminator is not hot from use. Use a clean, dry cloth. Ensure that the ventilation holes are not blocked with dust. Vacuum the openings, if necessary, from the outside of the unit. When not in use, cover the output port of the APEX2. Always be sure to remove the output port cover before turning on the lamp.

7.3 LAMP CARE AND HANDLING

Do not allow any contaminants or fingerprints to adhere to the lamp envelope or reflector. Always wear powder-free gloves when handling lamps. Handle the lamp by holding the outside of the reflector only. If a lamp becomes contaminated, do not use it before cleaning its envelope with isopropyl alcohol. Dry completely before using.

If contaminants are not removed, it may lead to reduced light output, overheating, damage to the envelope and premature failure. The lamp's reflector is coated and should not be wiped or touched at all. Remove any particulates such as dust using a bulb blower.

7.4 FUSE REPLACEMENT

The fuse compartment may be accessed from the back of the APEX 2 as shown in Figure 30. Only qualified personnel should access the fuses.



Figure 30: Fuse Compartment

8 SPECIFICATIONS

8.1 APEX2 ILLUMINATOR

Parameter	APEX2-XE Specification	APEX2-QTH Specification	
Light Source	100 watt Xenon lamp with integrated reflector	100 watt Quartz Tungsten Halogen lamp with integrated reflector	
Lamp Model	6252	6338	
Lamp Lifetime (Average)	1000 hours	500 hours	
External Lamp Intensity Control	None	0 to 5 VDC control signal 0 VDC = no lamp output 5 VDC = 100 watt lamp output	
Divergence (Half Angle)	5.0° ± 0.5°	5.0° ± 0.5°	
Spot Size (measured at 30 mm from output flange)	41.5 ± 2 mm diameter	41.5 ± 2 mm diameter	
Light Ripple (rms)	< 0.2%	< 0.07%	
Temporal Stability	< 1%		
Lens Material	Fused Silica		
Lens Transmittance Range	200 to 2500 nm		
Number of Filters	Holds up to six (6) filters, ordered separately. Uses maximum five (5) with MS257 monochromator		
Filter Diameter	1 inch [25.4 mm]		
Filter Thickness	0.23 inch [6.0 mm] maximum		
Connection Flange	Oriel 1.5-Inch Series Female Flange		
Shutter	Manually Controlled		
AC Input and	100 to 120 VAC, 50 to 60 Hz / 1.5 A, 250 V Time Delay Fuse		
5x20 mm Fuses (quantity 2)	200 to 240 VAC, 50 to 60 Hz / 0.8 A, 250 V Time Delay Fuse		
Operating Environment	5 to 40°C [41 to 104°F], indoor use only < 80% relative humidity (non-condensing) < 3000 m [9843 ft] altitude		
IEC Classification	Installation Category II, Pollution Degree 2		
Storage Temperature	0 to 50°C [32 to 122°F]		
Size	22.49 x 6.57 x 8.92 inch [571 x 167 x 227 mm]		
Weight	13 lb [5.9 kg]		
Optical Axis Height	4 inch [102 mm]		
Safety Interlock	Lamp shuts off when cover is removed or when internal temperature exceeds normal operating conditions		
CE Compliance	Yes		
RoHS Compliance	Yes		

8.2 UNIVERSAL FILTER WHEEL UTILITY SOFTWARE

Parameter	Specification
	Microsoft Windows XP, Service Pack 3
Operating System	Microsoft Windows 7, 32-bit and 64-bit
	Deguiros Migrosoft, not Framowork 4.0
	Requires Microsoft .net Framework 4.0
Processor Speed	2 GHz minimum
Random Access Memory (RAM)	1 GB minimum
Peripheral Hardware	USB 2.0 port
Hard Drive Space	800 MB minimum

Note:

One USB 2.0 port is required to connect between the computer and APEX2 filter wheel. Additional USB ports may be required when controlling other instruments, such as a monochromator, lock-in amplifier, power meter, etc.

9 EU DECLARATION OF CONFORMITY

EC DECLARATION OF CONFORMITY

Manufacturer's name: Newport Corporation

Manufacturer's address: 150 Long Beach Boulevard

Stratford, CT 06615 USA

Declares that the product:

Product Name: APEX2 Illumination System

Model Numbers: APEX2-XE, APEX2-QTH

Type of equipment: Electrical equipment for measurement, control and

laboratory use in industrial locations

conforms to the following Product Specifications:

Safety: EN 61010-1:2010

EMC: EN 61326-1:2013

complies with the following Directives:

2014/30/EU EMC Directive 2006/95/EC Low Voltage Directive

and accordingly, carries the € mark

CE mark affixed: Beaune; April 10, 2014

John Park

Bruno Rety Authorized to compile technical

documentation

Engineering Manager, Oriel Products

Group Director, PPT Instrument and Motion

Europe

150 Long Beach Boulevard

Micro-Controle Division of Newport Corporation

Stratford, CT 06615 USA Zone Industrielle

45340 Beaune la Rolande, France

10 WARRANTY AND SERVICE

10.1 CONTACTING ORIEL INSTRUMENTS

Oriel Instruments belongs to Newport Corporation's family of brands. Thanks to a steadfast commitment to quality, innovation, hard work and customer care, Newport is trusted the world over as the complete source for all photonics and laser technology and equipment.

Founded in 1969, Newport is a pioneering single-source solutions provider of laser and photonics components to the leaders in scientific research, life and health sciences, photovoltaics, microelectronics, industrial manufacturing and homeland security markets.

Newport Corporation proudly serves customers across Canada, Europe, Asia and the United States through 9 international subsidiaries and 24 sales offices worldwide. Every year, the Newport Resource catalog is hailed as the premier sourcebook for those in need of advanced technology products and services. It is available by mail request or through Newport's website. The website is where one will find product updates, interactive demonstrations, specification charts and more.

To obtain information regarding sales, technical support or factory service, United States and Canadian customers should contact Oriel Instruments directly.

Oriel Instruments 1791 Deere Avenue Irvine, CA 92606

Telephone: (800)-222-6440 (toll-free in United States)

Fax: (949) 253-1680

Sales/Technical Assistance: oriel.sales@newport.com

Repair Service: service@newport.com

Customers outside of the United States must contact their regional representative for all sales, technical support and service inquiries. A list of worldwide representatives can be found on Newport's website: http://www.newport.com/locations/worldwidecontacts.aspx.

10.2 REQUEST FOR ASSISTANCE / SERVICE

Please have the following information available when requesting assistance or service:

Contact information for the owner of the product.

Instrument model number (located on the product label).

Product serial number and date of manufacture (located on the product label).

Description of the problem.

To help Oriel's Technical Support Representatives diagnose the problem, please note the following:

Is the system used for manufacturing or research and development?
What was the state of the system right before the problem?
Had this problem occurred before? If so, when and how frequently?
Can the system continue to operate with this problem, or is it non-operational?
Were there any differences in the application or environment before the problem occurred?

10.3 REPAIR SERVICE

This section contains information regarding factory service for this product. The user should not attempt any maintenance or service of the system beyond the procedures outlined in this manual. This product contains no user serviceable parts other than what is noted in this manual. Any problem that cannot be resolved should be referred to Oriel Instruments.

If the instrument needs to be returned for service, a Return Material Authorization (RMA) number must be obtained prior to shipment to Oriel Instruments. This RMA number must appear on both the shipping container and the package documents.

Return the product to Oriel Instruments, freight prepaid, clearly marked with the RMA number and it either will be repaired or replaced it at Oriel's discretion.

Oriel is not responsible for damage occurring in transit. The Owner of the product bears all risk of loss or damage to the returned Products until delivery at Oriel's facility. Oriel is not responsible for product damage once it has left the facility after repair or replacement has been completed.

Oriel is not obligated to accept products returned without an RMA number. Any return shipment received by Oriel without an RMA number may be reshipped by Newport, freight collect, to the Owner of the product.

10.4 NON-WARRANTY REPAIR

For Products returned for repair that are not covered under warranty, Newport's standard repair charges shall be applicable in addition to all shipping expenses. Unless otherwise stated in Newport's repair quote, any such out-of-warranty repairs are warranted for ninety (90) days from date of shipment of the repaired Product.

Oriel will charge an evaluation fee to examine the product and determine the most appropriate course of action. Payment information must be obtained prior to having an RMA number assigned. Customers may use a valid credit card, and those who have an existing account with Newport Corporation may use a purchase order.

When the evaluation had been completed, the owner of the product will be contacted and notified of the final cost to repair or replace the item. If the decision is made to not proceed with the repair, only the evaluation fee will be billed. If authorization to perform the repair or provide a replacement is obtained, the evaluation fee will be applied to the final cost. A revised purchase order must be submitted for the final cost. If paying by credit card, written authorization must be provided that will allow the full repair cost to be charged to the card.

10.5 WARRANTY REPAIR

If there are any defects in material or workmanship or a failure to meet specifications, notify Oriel Instruments promptly, prior to the expiration of the warranty.

Except as otherwise expressly stated in Oriel's quote or in the current operating manual or other written guarantee for any of the Products, Oriel warrants that, for the period of time set forth below with respect to each Product or component type (the "Warranty Period"), the Products sold hereunder will be free from defects in material and workmanship, and will conform to the applicable specifications, under normal use and service when correctly installed and maintained. Oriel shall repair or replace, at Oriel's sole option, any defective or nonconforming Product or part thereof which is returned at Buyer's expense to Oriel facility, provided, that Buyer notifies Oriel in writing promptly after discovery of the defect or nonconformity and within the Warranty Period. Products may only be returned by Buyer when accompanied by a return material authorization number ("RMA number") issued by Oriel, with freight prepaid by Buyer. Oriel shall not be responsible for any damage occurring in transit or obligated to accept Products returned for warranty repair without an RMA number. Buyer bears all risk of loss or damage to the Products until delivery at Oriel's facility. Oriel shall pay for shipment back to Buyer for Products repaired under warranty.

WARRANTY PERIOD

All Products (except consumables such as lamps, filters, etc.) described here are warranted for a period of twelve (12) months from the date of shipment or 3000 hours of operation, whichever comes first.

Lamps, gratings, optical filters and other consumables / spare parts (whether sold as separate Products or constituting components of other Products) are warranted for a period of ninety (90) days from the date of shipment.

WARRANTY EXCLUSIONS

The above warranty does not apply to Products which are (a) repaired, modified or altered by any party other than Oriel; (b) used in conjunction with equipment not provided or authorized by Oriel; (c) subjected to unusual physical, thermal, or electrical stress, improper installation, misuse, abuse, accident or negligence in use, storage, transportation or handling, alteration, or tampering, or (d) considered a consumable item or an item requiring repair or replacement due to normal wear and tear.

DISCLAIMER OF WARRANTIES: EXCLUSIVE REMEDY

THE FOREGOING WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES. EXCEPT AS EXPRESSLY PROVIDED HEREIN, ORIEL MAKES NO WARRANTIES, EITHER EXPRESS OR IMPLIED, EITHER IN FACT OR BY OPERATION OF LAW, STATUTORY OR OTHERWISE, REGARDING THE PRODUCTS, SOFTWARE OR SERVICES. NEWPORT EXPRESSLY DISCLAIMS ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE FOR THE PRODUCTS, SOFTWARE OR SERVICES. THE OBLIGATIONS OF ORIEL SET FORTH IN THIS SECTION SHALL BE ORIEL'S SOLE LIABILITY. AND BUYER'S SOLE REMEDY. FOR BREACH OF WARRANTY. Representations and warranties made by any person including distributors, dealers and representatives of Oriel / Newport Corporation which are inconsistent or in conflict with the terms of this warranty shall not be binding on Oriel unless reduced to writing and approved by an expressly an authorized officer of Newport.

10.6 LOANER / DEMO MATERIAL

Persons receiving goods for demonstrations or temporary use or in any manner in which title is not transferred from Newport shall assume full responsibility for any and all damage while in their care, custody and control. If damage occurs, unrelated to the proper and warranted use and performance of the goods, recipient of the goods accepts full responsibility for restoring the goods to their original condition upon delivery, and for assuming all costs and charges.

Confidentiality & Proprietary Rights

Reservation of Title:

The Newport programs and all materials furnished or produced in connection with them ("Related Materials") contain trade secrets of Newport and are for use only in the manner expressly permitted. Newport claims and reserves all rights and benefits afforded under law in the Programs provided by Newport Corporation.

Newport shall retain full ownership of Intellectual Property Rights in and to all development, process, align or assembly technologies developed and other derivative work that may be developed by Newport. Customer shall not challenge, or cause any third party to challenge the rights of Newport.

Preservation of Secrecy and Confidentiality and Restrictions to Access:

Customer shall protect the Newport Programs and Related Materials as trade secrets of Newport, and shall devote its best efforts to ensure that all its personnel protect the Newport Programs as trade secrets of Newport Corporation. Customer shall not at any time disclose Newport's trade secrets to any other person, firm, organization, or employee that does not need (consistent with Customer's right of use hereunder) to obtain access to the Newport Programs and Related Materials. These restrictions shall not apply to information (1) generally known to the public or obtainable from public sources; (2) readily apparent from the keyboard operations, visual display, or output reports of the Programs; 3) previously in the possession of Customer or subsequently developed or acquired without reliance on the Newport Programs; or (4) approved by Newport for release without restriction.

First printing 2015

© 2015 by Newport Corporation, Irvine, CA. All rights reserved.

No part of this manual may be reproduced or copied without the prior written approval of Newport Corporation.

This manual has been provided for information only and product specifications are subject to change without notice. Any change will be reflected in future printings.

Newport Corporation 1791 Deere Avenue Irvine, CA, 92606 USA