



# **RoHS**

## **(Restriction of Hazardous Substances)**

### **Certificate of Compliance**

MKS Instruments, Inc. hereby certifies that the products listed in the attached table are compliant with the European Union's RoHS Directive, (EU) 2015/863 amending Annex II to Directive 2011/65/EU of the European Parliament and of the Council regarding the restriction of the use of certain hazardous substances in electrical and electronic equipment. The products listed below are compliant to RoHS requirements for concentration limitations, by weight of homogeneous material, of the ten substances shown on the following page.

#### **Model Number**

(PN if no Model assigned)

TF-36-28-I

TF-38-28-I

TF-46-28-I

TF-48-28-I

TF-410-28-I

TF-56-28-I

TF-58-28-I

TF-510-28-I

TF-36-24-I

TF-38-24-I

TF-46-24-I

TF-48-24-I

TF-410-24-I

TF-56-24-I

TF-58-24-I

TF-510-24-I

#### **Product Description**

Table frame support, for 3'x 6' table size, 28" tall, isolated

Table frame support, for 3'x 8' table size, 28" tall, isolated

Table frame support, for 4'x 6' table size, 28" tall, isolated

Table frame support, for 4'x 8' table size, 28" tall, isolated

Table frame support, for 4'x 10' table size, 28" tall, isolated

Table frame support, for 5'x 6' table size, 28" tall, isolated

Table frame support, for 5'x 8' table size, 28" tall, isolated

Table frame support, for 5'x 10' table size, 28" tall, isolated

Table frame support, for 3'x 6' table size, 24" tall, isolated

Table frame support, for 3'x 8' table size, 24" tall, isolated

Table frame support, for 4'x 6' table size, 24" tall, isolated

Table frame support, for 4'x 8' table size, 24" tall, isolated

Table frame support, for 4'x 10' table size, 24" tall, isolated

Table frame support, for 5'x 6' table size, 24" tall, isolated

Table frame support, for 5'x 8' table size, 24" tall, isolated

Table frame support, for 5'x 10' table size, 24" tall, isolated



The thresholds shown below are not in place for any legally allowable exemptions per Annex III of the aforementioned directive. If such exemptions are in use, they are noted on the attached table. If no exemptions are in use, then no further information is provided.

All information provided in this Certificate of Compliance is accurate to MKS' knowledge as of the date of this certification. This confirmation is made based on our internal engineering analysis of the individual items possibly being present along with the best technical information made available to MKS from its material suppliers.

Gwen Briens  
Vice-President and General Manager  
Instruments, Motion and CVC BU

March 7, 2025

Date

#### **LIST OF SUBSTANCES BANNED BY ROHS DIRECTIVE EU 2015/863**

(Item cannot exceed 0.1% of homogeneous material – except as noted)

- Lead (Pb)
- Mercury (Hg)
- Cadmium (Cd) – 0.01% limit
- Hexavalent chromium (Cr6+)
- Polybrominated biphenyls (PBB)
- Polybrominated diphenyl ether (PBDE)
- Diisobutyl phthalate (DIBP)
- Bis (2-ethylhexyl) phthalate (DEHP)
- Butyl benzyl phthalate (BBP)
- Dibutylphthalate (DBP)



## MKS ROHS DIRECTIVE 2011/65/EU PRODUCT EXEMPTIONS

| Model Number<br>(PN if no Model assigned) | Product Description                                            | Annex III<br>Exemption<br># | Annex III<br>Exemption Description                                                                                        |
|-------------------------------------------|----------------------------------------------------------------|-----------------------------|---------------------------------------------------------------------------------------------------------------------------|
| TF-36-28-I                                | Table frame support, for 3'x 6' table size, 28" tall, isolated | 6(A)                        | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|                                           |                                                                | 6(B)                        | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|                                           |                                                                | 6(C)                        | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-38-28-I                                | Table frame support, for 3'x 8' table size, 28" tall, isolated | 6(A)                        | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|                                           |                                                                | 6(B)                        | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|                                           |                                                                | 6(C)                        | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-46-28-I                                | Table frame support, for 4'x 6' table size, 28" tall, isolated | 6(A)                        | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|                                           |                                                                | 6(B)                        | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|                                           |                                                                | 6(C)                        | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |



|             |                                                                 |      |                                                                                                                           |
|-------------|-----------------------------------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------|
| TF-48-28-I  | Table frame support, for 4'x 8' table size, 28" tall, isolated  | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-410-28-I | Table frame support, for 4'x 10' table size, 28" tall, isolated | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-56-28-I  | Table frame support, for 5'x 6' table size, 28" tall, isolated  | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |



|             |                                                                 |      |                                                                                                                           |
|-------------|-----------------------------------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------|
| TF-58-28-I  | Table frame support, for 5'x 8' table size, 28" tall, isolated  | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-510-28-I | Table frame support, for 5'x 10' table size, 28" tall, isolated | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-36-24-I  | Table frame support, for 3'x 6' table size, 24" tall, isolated  | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |



|            |                                                                |      |                                                                                                                           |
|------------|----------------------------------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------|
| TF-38-24-I | Table frame support, for 3'x 8' table size, 24" tall, isolated | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|            |                                                                | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|            |                                                                | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-46-24-I | Table frame support, for 4'x 6' table size, 24" tall, isolated | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|            |                                                                | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|            |                                                                | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-48-24-I | Table frame support, for 4'x 8' table size, 24" tall, isolated | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|            |                                                                | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|            |                                                                | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |



|             |                                                                 |      |                                                                                                                           |
|-------------|-----------------------------------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------|
| TF-410-24-I | Table frame support, for 4'x 10' table size, 24" tall, isolated | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-56-24-I  | Table frame support, for 5'x 6' table size, 24" tall, isolated  | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |
| TF-58-24-I  | Table frame support, for 5'x 8' table size, 24" tall, isolated  | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |



|             |                                                                 |      |                                                                                                                           |
|-------------|-----------------------------------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------|
| TF-510-24-I | Table frame support, for 5'x 10' table size, 24" tall, isolated | 6(A) | LEAD AS AN ALLOYING ELEMENT IN STEEL FOR MACHINING PURPOSES AND IN GALVANIZED STEEL CONTAINING UP TO 0.35% LEAD BY WEIGHT |
|             |                                                                 | 6(B) | ALUMINUM ALLOY CONTAINING UP TO .4% LEAD BY WEIGHT                                                                        |
|             |                                                                 | 6(C) | COPPER ALLOY CONTAINING UP TO 4% LEAD BY WEIGHT                                                                           |